

S-Video Extender over Cat 5

StarTech ID: SVIDUTPEXT



The SVIDUTPEXT S-Video Extender over Cat 5 lets you extend an S-Video source signal up to 200 meters over Cat 5 cable, allowing you to configure your S-Video A/V setup as needed.

The S-Video over Cat 5 extender is comprised of two extender units that can be used interchangeably - one is installed near the video signal source, the other to be placed near the desired display, up to an impressive 200m away. With no software or power adapter requirements, installation and setup is quick and hassle-free. The included installation/mounting kit, and 20cm S-Video cable offer flexibility in the placement of the transmitter and receiver units.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for classrooms, projectors, tradeshow, and retail displays using an S-video signal
- To be used in home or commercial applications as a fast, and cost-effective means of connecting S-video equipment over long distances

Features

- Extend video to 200 meters using a cat5 cable
- Installation is a breeze, no software, and no power adapter required
- Works with shielded twisted pair (STP) and unshielded twisted pair (UTP) cat5 cable
- Mounting kit included for wall installation
- Includes two 20cm s-video cables for quick setup and placing extender right next to your source and display

Technical Specifications

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP or better
Audio	No
Daisy-Chain	No
Local Unit Connectors	1 - RJ-45 Female
Local Unit Connectors	1 - S-Video (4 pin; Mini-DIN) Male
Remote Unit Connectors	1 - RJ-45 Female
Remote Unit Connectors	1 - S-Video (4 pin; Mini-DIN) Male
Max Distance	200 m / 660 ft
Maximum Analog Resolutions	480i/480p
Supported Resolutions	480i/480p
Color	Black
Product Length	2.7 in [69 mm]
Product Width	1 in [2.5 cm]
Product Height	0.9 in [22 mm]
Product Weight	2.8 oz [80 g]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - S-Video over Cat5 Extender (local and remote)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

