

3.5in Black USB 2.0 to IDE SATA External Hard Drive Enclosure

StarTech ID: UNI3510U2



This hybrid, 3.5in USB 2.0 to IDE/SATA Hard Drive Enclosure lets you turn almost any 3.5in hard drive into a portable storage device! Compatible with both IDE (66/100/133) or SATA (SATA, SATA II, SATA III) hard drives, the enclosure offers a cost-effective and convenient choice for a variety of uses including data backups, digital image storage, multimedia storage, or simply putting an "outdated" drive to good use.

The UNI3510U2 IDE/SATA hard drive enclosure is designed and built to provide extreme durability and stability, while remaining an attractive addition to any environment with a stylish aluminum casing and fixed luminescent base that glows an eye-catching blue while the enclosure is powered.

Applications and Solutions

- Turn an unused IDE (PATA) or SATA hard drive into additional external storage
- Technicians who work with and need to access a variety of different drives
- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on storage to any USB enabled computer system
- Backup data to an external storage device for archiving or freeing up space

Features

- Accepts either SATA or IDE (PATA) drives
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA 1.5/3.0/6.0Gbps or IDE 66/100/133 Mbps hard drives
- Supports 3.5" form factor hard drives
- Plug-and-Play and Hot-Swap compatible
- Compact, light-weight design

Technical Specifications

- Warranty: 2 Years
- Number of internal 3.5 inch bays: 1
- Max Drive Capacity: 1.0 Terabyte hard drives

Tested:Western Digital (WD10EACS) 16Mb Cache 7200RPM

Hitachi Deskstar 7K1000 32Mb Cache 7200 RPM

- Product Height: 5.5 in [139.7 mm]
- Product Length: 8.75 in [222.25 mm]
- Maximum Data Transfer Rate: 480 Mbps
- Number of Drives: 1
- Output Current: 2000mA
- Carton Quantity: 10
- Shipping (Package) Weight: 3.01 lb [1.36 kg]
- Product Weight: 26.42 oz [748.43 g]
- Product Width: 1.5 in [38 mm]

