

3.5in Black USB 2.0 to IDE SATA External Hard Drive Enclosure

StarTech ID: UNI3510U2



This hybrid, 3.5in USB 2.0 to IDE/SATA Hard Drive Enclosure lets you turn almost any 3.5in hard drive into a portable storage device! Compatible with both IDE (66/100/133) or SATA (SATA, SATA II, SATA III) hard drives, the enclosure offers a cost-effective and convenient choice for a variety of uses including data backups, digital image storage, multimedia storage, or simply putting an "outdated" drive to good use. Large capacity drives (tested with up to 4TB) can be used to greatly enhance your computer's storage/backup capabilities.

The UNI3510U2 IDE/SATA hard drive enclosure is designed and built to provide extreme durability and stability, while remaining an attractive addition to any environment with a stylish aluminum casing and fixed luminescent base that glows an eye-catching blue while the enclosure is powered.

Applications

- Turn an unused IDE (PATA) or SATA hard drive into additional external storage
- Technicians who work with and need to access a variety of different drives
- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on storage to any USB enabled computer system
- Backup data to an external storage device for archiving or freeing up space

Features

- Accepts either SATA or IDE (PATA) drives
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA 1.5/3.0/6.0Gbps or IDE 66/100/133 Mbps hard drives
- Supports 3.5" form factor hard drives
- Plug-and-Play and Hot-Swap compatible
- Compact, light-weight design

Technical Specifications

Warranty	2 Years
Interface	USB 2.0
Number of Drives	1
Drive Size	3.5in
Drive Type	SATA & IDE
Drive Installation	Fixed
Number of internal 3.5 inch bays	1
Fan(s)	No
Drive Connectors	1 - IDE (40 Pin; EIDE/PATA) Female
Drive Connectors	1 - LP4 (4 pin; Molex Large Drive Power) Female
Drive Connectors	1 - SATA (7 pin; Data) Receptacle
Drive Connectors	1 - SATA Power (15 pin) Receptacle
Host Connectors	1 - USB B (4 pin) Female
Maximum Data Transfer Rate	480 Mbps
RAID	No
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM hard drives
Color	Black
Enclosure Type	Aluminum
Product Length	8.7 in [222.3 mm]
Product Width	1.5 in [38 mm]
Product Height	5.5 in [139.7 mm]
Product Weight	26.4 oz [748.4 g]
Power Adapter Included	Yes
Input Voltage	115 AC
Output Voltage	12 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	L
Shipping (Package) Weight	3 lb [1.4 kg]
Included in Package	1 - SATA/IDE to USB 2.0 External HDD Enclosure
Included in Package	1 - IDE Cable (Internal)
Included in Package	1 - LP4 Power Adapter Cable (Internal)
Included in Package	1 - SATA Data Cable (Internal)
Included in Package	1 - SATA Power Adapter Cable (Internal)

Included in Package	1 - USB 2.0 Cable
Included in Package	1 - Mounting Screw Kit
Included in Package	1 - AC Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

