

## USB to SATA IDE Hard Drive Docking Station for 2.5in or 3.5in HDD Dock

StarTech ID: UNIDOCK2U



The UNIDOCK2U HDD Docking Station delivers full, instant access to any 2.5" and/or 3.5" IDE or SATA hard drive without having to mount the drive in a computer, or install it in an external enclosure.

Connected to the host computer through a single USB 2.0 connection, both an IDE hard drive and a SATA hard drive (SATA, SATA II, SATA III) can be connected to the HDD dock simultaneously - a convenient solution for migrating data from an IDE drive to a SATA drive or vice versa, or simply harnessing fast and simple access to the contents on both hard drives.

The hard drive docking station provides the ideal solution for any laptop or desktop application, with support for plug and play hard drive installation on most operating systems to ensure easy hard drive swapping and convenient access to valuable data.

### Applications and Solutions

- Quick access to 2.5/3.5" drives to retrieve data from
- Transfer files directly between a SATA and IDE hard drive, without having to transfer to the host computer first, or using multiple devices
- Data recovery specialists who need quick access to drives for imaging

- Backup data quickly to an external drive for archiving
- Technicians who test or benchmark multiple hard drives

## **Features**

- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) or solid state drives (SSD)
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with PATA (IDE) 66/100/133 MBps hard drives
- Front panel IDE data and power connectors
- Patented drive ejection mechanism
- Combined power switch and status LED
- Top slot-loading SATA drive connector
- Compact, desktop-style form factor
- Plug-and-Play and hot-swap compatible

## Technical Specifications

- Warranty: 2 Years
- Chipset ID: JMicron - JM20337
- Product Height: 2.56 in [65 mm]
- Humidity: 8~90% RH
- Insertion Rating: 15,000 Cycles
- LED Indicators: 1 - Power and Drive Activity
- Product Length: 5.71 in [145 mm]
- Operating Temperature: 5&deg;C to 80&deg;C (41&deg;F to 176&deg;F)
- OS Compatibility: Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and MAC OS X and up
- Output Current: 3000mA
- Carton Quantity: 10
- Storage Temperature: -40&deg;C to 70&deg;C (-40&deg;F to 158&deg;F)
- Shipping (Package) Weight: 37.77 oz [1070 g]
- Product Weight: 14.58 oz [413 g]
- Product Width: 3.66 in [93 mm]

