

USBthere - 1 Port 330 Foot (100 Meter) Powered USB Extender

StarTech ID: USB201EXT



Boost the distance of your USB connection with the USBthere, a one-port powered USB extender from StarTech.com. You'll be able to place your high power USB devices up to 330 feet (100m) away from your computer, an incredible 20 times greater than normal USB length restrictions. The Local and Remote units connect using standard Cat 5e Ethernet Cable and there's no need to buy additional hubs, repeaters or software, you just plug in and go.

Perfect for USB video cameras, scanners, and POS equipment, the USBthere maintains the USB 1.1 standard with data transfer rates of up to 12 Mbits/sec. With the USBthere, extending the range of your USB devices has never been easier.

Applications

- Ideal for use with remote digital recorders, security and surveillance equipment, POS devices, printers, scanners as well as any other USB peripheral

Features

- Extends the range of one USB device up to 330 feet (100 meters) using standard Cat 5e Ethernet cables
- Allows users to make use of existing Ethernet infrastructure for extending USB devices
- Compliant with USB 1.1 specifications
- Data transfer rates of up to 12 Mbits/sec
- Easy installation and set up with no software required
- Comes complete with a 6 foot USB cable and an external power adapter

Technical Specifications

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP
Industry Standards	USB 1.1
Maximum Data Transfer Rate	12000000 Mbits/Sec
Maximum Cable Length	328 ft [100 m]
Max Distance	100 m / 330 ft
General Specifications	1.2 lbs (0.6 kg)
General Specifications	15V DC
General Specifications	2.4 lbs (0.8 kg)
General Specifications	330 ft (100 m)
General Specifications	4.2 x 3.3 x 1.3 Inches (107 x 84 x 34 mm)
General Specifications	500 mA
General Specifications	Supports USB 1.0 and USB 1.1 devices (multi-speed)
General Specifications	Up to 12 Mbits/sec
General Specifications	Up to 4 hubs connected to the local unit
General Specifications	Upstream: 1 x RJ-45 Downstream: 2 x 6 pin USB (Type A)
General Specifications	Upstream: 1 x 4 pin USB (Type B) Downstream: 1 x RJ-45
Color	Black
Enclosure Type	Steel
Product Length	4.2 in [107 mm]
Product Width	3.3 in [8.4 cm]
Product Height	1.3 in [34 mm]
Product Weight	10.6 oz [300 g]
LED Indicators	1 - Host
LED Indicators	1 - Link
LED Indicators	1 - Power
Operating Temperature	4 to 40 °C
Shipping (Package) Weight	2.4 lb [1.1 kg]
Included in Package	1 - Local Extender unit
Included in Package	1 - Remote Extender unit
Included in Package	1 - 6 ft USB Cable
Included in Package	1 - 15V DC (1A) Power Adapter

Included in Package 1 - User's Guide

Certifications, Reports and Compatibility

