

16 ft USB 2.0 Active Extension Cable - M/F

StarTech ID: USB2FAAEXT15



This 16ft USB 2.0 Active Extension Cable offers one USB A male connector and one USB A female connector, providing an active, bus-powered extension of a USB 2.0 device connection by up to 16ft (5m).

The extension cable (USB Extender) supports high speed USB 2.0 transfer rates of up to 480Mbps, and is backed by StarTech.com's 2-year Warranty.

Applications

- Connect printer, scanners or other USB devices that are just out of reach of regular USB cables
- Extend the distance of USB peripherals where external power is not available/practical

Features

- Powered directly from the USB port
- Cascadable up to 5 levels
- High Speed USB 2.0 compliant host interface, with supported data transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Plug and Play compatible

Technical Specifications

Warranty	2 Years
Connector Type(s)	1 - USB A (4 pin) Female
Connector Type(s)	1 - USB A (4 pin) Male
Type and Rate	USB 2.0 - 480 Mbit/s
OS Compatibility	OS independent; No software or drivers required
Cable Length	16 ft [4.9 m]
Product Length	2.4 in [60 mm]
Product Width	1.2 in [30 mm]
Product Height	0.9 in [22 mm]
Product Weight	6.2 oz [177 g]
System and Cable Requirements	1 x Free USB port
Note	Cascade up to 5 USB2FAAEXT15 devices together for further extension
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - 1 x 16 Foot (5 Meter) USB 2.0 Active Extension Cable

Certifications, Reports and Compatibility

