

3 ft A Right Angle to B Right Angle USB Cable - M/M

StarTech ID: *USB2HAB2RA3*



The USB2HAB2RA3 Right Angle USB Cable offers a neat, space-saving solution, especially for laptop peripheral connections.

Featuring one right-angled USB 'A' type connector and one right-angled USB 'B' type connector, this 3ft cable allows the desktop or laptop computer and the connected USB peripheral to be positioned nearly flush against a wall or other surface, by eliminating the space that would typically be required to accommodate a 'straight' connection from the cable into the USB port or peripheral device.

This high quality cable is backed by lifetime warranty.

Applications

- Designed for use in application where space is limited

Features

- Molded 905/8/2012eg; connectors with strain relief
- Designed and constructed to USB 2.0 specifications
- Lifetime warranty

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Foil shielded twisted pair
Connector A	1 - USB A (4 pin) Male
Connector B	1 - USB B (4 pin) Male
Type and Rate	USB 2.0 - 480 Mbit/s
Color	Black
Wire Gauge	24/28 AWG
Cable Length	3 ft [0.9 m]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - Right angled USB A to B cable

Certifications, Reports and Compatibility

