

## SATA USB Adapter Cable with Power Adapter

StarTech ID: USB2SATA25



The USB2SATA25 USB-SATA Adapter Cable connects any standard 2.5in or 3.5in SATA hard drive to a computer through USB 2.0.

The USB to SATA adapter lets you connect a bare drive with no enclosure, saving time and hassle.

The adapter cable works with Windows and Mac computers and does not require driver installation - a true plug-and-play solution for adding cost-effective external storage or overcoming incompatibility between modern hard drives and motherboards that may not be SATA-equipped or have a Serial ATA port available.

### Applications

- Connect a 2.5 inch or 3.5 inch SATA drive to a USB 2.0 port
- Testing and quickly swapping SATA hard drives
- Plug in a Serial ATA hard drive quickly and easily without taking your case apart
- Use your 2.5" and 3.5" SATA hard drives externally, with a laptop or desktop computer

### Features

- Includes all necessary interface and power connectors for your drives making it an all-in-one solution
- Included software for Windows enables cloning and one button backup feature for backing up and syncing files
- External power adapter included for connecting 3.5in SATA drives

## Technical Specifications

|                           |   |
|---------------------------|---|
| Warranty                  | 2 Years   |
| Connector Type(s)         | 1 - SATA Data & Power Combo (7+15 pin) Receptacle   |
| Connector Type(s)         | 2 - USB A (4 pin) Male  |
| General Specifications    | 480 Mbits/Sec   |
| General Specifications    | USB bus powered for 2.5 inch hard drive. Requires included power adapter for 3.5 inch hard drives and 5.25 inch optical drives. |
| General Specifications    | USB2SATA25 is backwards compatible with USB 1.1 standard, but not recommended due to slow transfer rate.                        |
| OS Compatibility          | Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 9.22 and up                         |
| Color                     | Black   |
| Product Length            | 10.5 in [266 mm]  |
| Product Width             | 2.2 in [55 mm]  |
| Product Height            | 0.7 in [18 mm]  |
| Product Weight            | 1.6 oz [45 g]   |
| Input Voltage             | 110 ~ 240 AC  |
| Power Adapter Included    | Yes   |
| Output Voltage            | 12 DC   |
| Output Current            | 2A  |
| Center Tip Polarity       | Positive  |
| Plug Type                 | M   |
| Operating Temperature     | 105/9/2012eg;C to 405/9/2012eg;C (505/9/2012eg;F to 1045/9/2012eg;F)  |
| Storage Temperature       | -105/9/2012eg;C to 805/9/2012eg;C (145/9/2012eg;F to 1765/9/2012eg;F)   |
| Humidity                  | 0~80% RH  |
| Shipping (Package) Weight | 450   |
| Included in Package 1     | USB to SATA Adapter   |
| Included in Package 1     | Power Adapter and Cable   |
| Included in Package 1     | Driver/Software CD  |
| Included in Package 1     | Instruction Manual  |

Certifications, Reports and Compatibility

