

6 ft USB VGA Adapter Cable - External Multi Monitor Video M/M

StarTech ID: *USB2VGAMM6*



The USB2VGAMM6 External USB VGA Adapter Cable offers a hassle-free multi-monitor solution, turning a USB 2.0 port into a VGA video connection. This 6-foot USB Display Adapter is a complete solution, ready to go out of the box with all the cables you need built right onto the adapter. Simply install the drivers, connect to your computer and display. Built-on cables make the USB2VGAMM6 easier to install and does away with the need to worry about forgetting a cable.

Instead of having to open the computer case to install a specialized video card to accommodate a multi-display configuration, USB2VGAMM6 functions as an external USB video card saving both time and hassle.

Multiple (USB2VGAMM6) adapters (up to 5 total) can be used on a single system to provide several mirrored displays or extended desktops - a convenient and cost-effective multi-VGA option for virtually any laptop or desktop operating environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Extend or mirror the image shown on an existing laptop or desktop display
- Run multiple applications on different screens, check your email on one display and work on a document in the other.

Features

- Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller
- Built-on USB and VGA cables
- Hassle-free installation
- No power adapter required

Technical Specifications

Warranty	2 Years
Memory	16MB RAM
Chipset ID	DisplayLink – DL165
Connector Type(s)	1 - USB A (4 pin) Male
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Male
Maximum Analog Resolutions	1600x1200(standard) or 1680x1050(wide) @ 32 bits
Supported Resolutions	Widescreen (16/32 bit): 1680x1050, 1440x900, 1366x768 Standard (16/32 bit): 1600x1200, 1280x1024, 1024x768, 800x600, 640x480
OS Compatibility	Windows 2000/ XP / Vista(32/64bit, Aero 3D interface supported)/ 7(32/64bit)/, and Mac OS X (Tiger 10.4.11 and Leopard 10.5.6)
Color	Black
Cable Length	6 ft [1.8 m]
Product Length	72 in [1829 mm]
Product Width	1.9 in [48 mm]
Product Height	0.9 in [23.5 mm]
Product Weight	3.5 oz [100 g]
System and Cable Requirements	Available USB 2.0 port 1.2Ghz or higher CPU 512MB RAM 30MB Hard Drive space
Note	Connect a maximum of five USB2VGAMM6 adapters on a single PC
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	1 - USB to VGA Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

