

3 ft SuperSpeed USB 3.0 Cable A to Micro B

StarTech ID: *USB3SAUB3*



The USB3SAUB3 3-foot SuperSpeed USB 3.0 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the USB 3.0 A to Micro B cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication to provide a quick and easy way to connect to an external storage solution with astounding throughputs of up to 4.8Gbps (when used with a USB 3.0 host and device).

Like all StarTech.com cables, the 3-foot USB 3.0 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Applications

- Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Features

- Shielded Twisted Pair (STP) design, helping to eliminate electro-magnetic interference (EMI)
- Data transfer rates up to 5Gbps
- Backwards compatible with USB 2.0
- Molded connectors with strain relief

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Connector B	1 - USB 3.0 Micro-B (10 pin; SuperSpeed) Male
Type and Rate	USB 3.0 - 5 Gbit/s
Color	Blue
Wire Gauge	28 AWG
Cable Length	3 ft [0.9 m]
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - 3 ft SuperSpeed USB 3.0 Cable A to Micro B

Certifications, Reports and Compatibility

