

6 ft SuperSpeed USB 3.0 Extension Cable A to A - M/F

StarTech ID: USB3SEXTAA6



StarTech.com's 6ft SuperSpeed USB 3.0 extension cable (A-A) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, extends a USB 3.0 cable connection by 6ft, delivering a throughput of up to 4.8Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.0 extension cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

Like all StarTech.com cables, the 6ft USB 3.0 extension cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Applications

- Extend your USB 3.0 Super Speed cable by 6ft

Features

- Cable and Connectors our compliant with USB 3.0 SuperSpeed specifications

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Foil shielded twisted pair
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Connector B	1 - USB 3.0 A (9 pin; SuperSpeed) Female
Type and Rate	USB 3.0 - 4.8 Gbit/s
Color	Blue
Wire Gauge	28 AWG
Cable Length	6 ft [1.8 m]
Product Weight	0.2 lb [0.1 kg]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - USB 3.0 Super Speed Extension cable

Certifications, Reports and Compatibility

