

VGA PC to TV Video Converter with Remote Control

StarTech ID: VGA2NTSCPRO



This High Resolution VGA to TV Video Converter/Scaler accepts your computer's VGA signal and converts the graphics data into TV video format (composite, S-Video, and analog RGB for SCART implementation).

A versatile video solution, the VGA to TV video converter/scaler supports NTSC, PAL and SECAM video systems, acting as a VGA to NTSC/PAL Converter and features adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control - allowing you to tweak the video as needed to suit your display.

A practical tool for synchronizing your monitor and television screens, the converter/scaler provides simultaneous display on both TV screen and PC monitor, and features a handy remote control that allows you to make adjustments from a distance.

Applications and Solutions

- An inexpensive way to increase the size of a computer display
- Displays computer screen images on your TV
- Great for boardroom meetings, tradeshows and lectures
- Use your TV to display computer presentations, surfing the Internet, playing video games and more

Features

- 4 times zoom function support
- Adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control
- Handy remote control allows you to make adjustments from a distance
- Provides output in both composite and S-Video formats
- Simultaneous display on both TV screen and PC monitor
- Supports NTSC, PAL and SECAM video systems. SECAM systems display by analog RGB output port
- True color quality

Technical Specifications

- Warranty: 1 Year warranty
- Color: Beige
- Product Height: 1.02 in [26 mm]
- Input Voltage: 115 AC
- Product Length: 6.5 in [165 mm]
- Maximum Analog Resolutions: 1152 x 864
- Output Current: 600mA
- Output Voltage: 9 DC
- Plug Type: M
- Power Adapter Included: Yes
- Center Tip Polarity: Positive
- Carton Quantity: 10
- Shipping (Package) Weight: 2.17 lb [0.98 kg]
- Product Width: 4.13 in [105 mm]
- Scan Rates: Up to 100Hz for 640x480 resolution
 - Up to 85Hz for 800x600 resolution
 - Up to 75Hz for 1024x768 resolution
 - Up to 60Hz for 1152x864 resolution
- Video Output: Composite video, S-Video and RGB for SCART
- Cables Included: 1 x 3ft HDDB15 Extension cable
 - 1 x 6ft Composite video cable
 - 1 x 6ft S-Video cable

- Power Supply: 9V DC power adapter included
- Dimensions: 6.5 x 4.1 x 1.0 inches(165 x 105 x 26mm)
- Compliance: FCC class B and CE
- Input Signal: VGA (HD-15 female connector)
- Horizontal Frequency: 25KHz - 58.464KHz
- Vertical Frequency: 50Hz - 100Hz

