

VGA PC to TV Video Converter with Remote Control

StarTech ID: *VGA2NTSCPRO*



This High Resolution VGA to TV Video Converter/Scaler accepts your computer's VGA signal and converts the graphics data into TV video format (composite, S-Video, and analog RGB for SCART implementation).

A versatile video solution, the VGA to TV video converter/scaler supports NTSC, PAL and SECAM video systems, acting as a VGA to NTSC/PAL Converter and features adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control - allowing you to tweak the video as needed to suit your display.

A practical tool for synchronizing your monitor and television screens, the converter/scaler provides simultaneous display on both TV screen and PC monitor, and features a handy remote control that allows you to make adjustments from a distance.

Applications

- Displays computer screen images on your TV
- An inexpensive way to increase the size of a computer display
- Use your TV to display computer presentations, surfing the Internet, playing video games and more
- Great for boardroom meetings, tradeshows and lectures

Features

- True color quality
- Simultaneous display on both TV screen and PC monitor
- Supports NTSC, PAL and SECAM video systems. SECAM systems display by analog RGB output port
- 4 times zoom function support
- Handy remote control allows you to make adjustments from a distance
- Provides output in both composite and S-Video formats
- Adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control

Technical Specifications

Warranty	2 Years
Audio	No
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - Composite Video (1 x RCA) Female
Connector B	1 - S-Video (4 pin; Mini-DIN) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	1152 x 864
Supported Resolutions	1152x864(=60Hz), 1024x768(=75Hz), 800x600(=85Hz), 640x480(=100Hz)
Frequency Range	Vertical 50Hz - 100Hz Horizontal 25KHz - 58.464KHz
Color	Beige
Product Length	6.5 in [165 mm]
Product Width	4.1 in [105 mm]
Product Height	1 in [26 mm]
Product Weight	7.7 oz [217 g]
Power Adapter Included	Yes
Input Voltage	115 AC
Output Voltage	9 DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Shipping (Package) Weight	2.2 lb [1 kg]
Included in Package	1 - VGA to NTSC/PAL Converter w/ Remote
Included in Package	1 - CR2025 3V Battery
Included in Package	1 - 4 pin M/M cable
Included in Package	1 - RCA cable M/M
Included in Package	1 - VGA cable 15 pin M/F
Included in Package	1 - 9V DC Adapter
Included in Package	1 - Manual

Certifications, Reports and Compatibility

