

4 Port VGA Video Audio Switch with RS232 control

StarTech ID: VS410RVGAA



The VS410RVGAA 4 Port VGA Video Audio Switch with RS232 control lets you switch between four separate VGA signals, as well as the corresponding audio, for output to a single display or projector at resolutions up to 1920x1200 (PC) or 1080p (HDTV).

An ideal solution for situations where VGA and audio input ports are scarce, the VGA switch eliminates the hassle of having to swap out connections to your display and audio receiver, while letting you select the video source quickly and easily at the push of a button.

The VGA switch also features convenient remote switching capabilities through either RS232 serial remote control, or the included IR remote control - allowing you to switch between VGA input signals from a distance and in turn providing a convenient addition to presentation displays, trade shows, security environments and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications and Solutions

- Great for use in presentations, trade shows, conferences, retail, and entertainment applications
- Excellent solution for connecting and switching between multiple PC/HDTV's to one display
- Perfect for use in boardroom settings to let visitors connect to your display or projector

Features

- Supports resolutions up to 1920x1200 (1080p)
- Supports VGA Video bandwidth of 650 MHz
- RS232 interface provides you with remote/off-site control
- 3.5mm audio connections
- Front panel push-buttons
- Includes an easy-to-use remote control for easy switching between devices

Technical Specifications

- Warranty: 2 Years
- Bandwidth: 650 MHz (-3dB) max
- Input Current: 0.6A
- Maximum Analog Resolutions: 1920x1200 (PC), and 1080p (HDTV)
- Output Current: 2.6A
- Power Consumption: 5W
- Carton Quantity: 3
- Shipping (Package) Weight: 5.08 lb [2.3 kg]

