

4 Port VGA Video Audio Switch with RS232 control

StarTech ID: VS410RVGAA



The VS410RVGAA 4 Port VGA Video Audio Switch with RS232 control lets you switch between four separate VGA signals, as well as the corresponding audio, for output to a single display or projector at resolutions up to 1920x1200 (PC) or 1080p (HDTV).

An ideal solution for situations where VGA and audio input ports are scarce, the VGA switch eliminates the hassle of having to swap out connections to your display and audio receiver, while letting you select the video source quickly and easily at the push of a button.

The VGA switch also features convenient remote switching capabilities through either RS232 serial remote control, or the included IR remote control - allowing you to switch between VGA input signals from a distance and in turn providing a convenient addition to presentation displays, trade shows, security environments and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Perfect for use in boardroom settings to let visitors connect to your display or projector
- Great for use in presentations, trade shows, conferences, retail, and entertainment applications
- Excellent solution for connecting and switching between multiple PC/HDTV's to one display

Features

- Supports resolutions up to 1920x1200 (1080p)
- Supports VGA Video bandwidth of 650 MHz
- Includes an easy-to-use remote control for easy switching between devices
- RS232 interface provides you with remote/off-site control
- Front panel push-buttons
- 3.5mm audio connections

Technical Specifications

Warranty	2 Years
Ports	4
Audio	Yes
Connector A	4 - 3.5 mm Mini-Jack (3 Position) Female
Connector A	4 - VGA (15 pin; High Density D-Sub) Female
Connector B	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	1920x1200 (PC), and 1080p (HDTV)
Bandwidth	650 MHz (-3dB) max
Color	Black
Enclosure Type	Aluminum
Product Length	6.5 in [165 mm]
Product Width	11.3 in [287 mm]
Product Height	1.6 in [40 mm]
Product Weight	52.9 oz [1498 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.6A
Output Voltage	5 DC
Output Current	2.6A
Center Tip Polarity	Positive
Power Consumption	5W
Shipping (Package) Weight	5.1 lb [2.3 kg]
Included in Package	1 - IR Remote Control
Included in Package	1 - 4x1 VGA Switch
Included in Package	1 - 3ft. VGA Cable
Included in Package	1 - Universal Power Adapter (US/UK/EU/AUS)

Certifications, Reports and Compatibility

