

4 Port High Resolution VGA Video Switch with Remote

StarTech ID: VS415RVGA



This 4 port VGA Video Switch allows you to select between four separate VGA video signals for output to a single monitor or projector up to 65m (213ft) away from the video source.

A perfect solution for situations where VGA input ports are at a premium, the 4 port VGA Video Switch eliminates the hassle of having to swap out connections to your display, and allows you to select your video source at the push of a front panel pushbutton or by using the included remote control.

Applications

- Excellent solution for connecting and switching between multiple PC's to one display.
- Great for use in presentations, tradeshow, conferences, retail, and entertainment applications.

Features

- Connect to your display at a maximum distance of 65 meters
- Switch between PC's by using the controls on the switcher or the included remote control
- Supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth
- Solid construction in a metal enclosure

Technical Specifications

Warranty	2 Years
Ports	4
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Connector Type(s)	4 - VGA (15 pin; High Density D-Sub) Male
Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	2048x1536
Bandwidth	450MHz
Color	Black
Product Length	5 in [127 mm]
Product Width	2.6 in [67 mm]
Product Height	1.7 in [42 mm]
Product Weight	17.6 oz [500 g]
Output Voltage	5 DC
Output Current	1A
Operating Temperature	05/8/2012eg;C to 405/8/2012eg;C (325/8/2012eg;F to 1045/8/2012eg;F)
Storage Temperature	-505/8/2012eg;C to 705/8/2012eg;C (-585/8/2012eg;F to 1585/8/2012eg;F)
Shipping (Package) Weight	1.6 lb [0.7 kg]
Included in Package	1 - 4 Port Video Selector
Included in Package	1 - Remote Control
Included in Package	1 - Power Adapter (5V DC, 1A)
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

