

## 2x4 Port Matrix DVI Audio Video Switch

StarTech ID: VS420RDVIA



This 2x4 Port Matrix DVI Audio Video Switch lets you select between two DVI-I sources for display on up to four monitors. At the push of a button, the DVI and audio matrix switch lets you select the audio and DVI input that will be delivered each display - providing the versatility needed to simplify digital signage configurations or multi-monitor presentations.

Providing simple, yet comprehensive control of DVI signal transmissions, the 2x4 matrix switch lets you independently toggle video (and audio) on or off for each display. This not only helps prolong the lifespan of the monitor but also reduces power consumption, delivering an economical and environmentally friendly solution.

StarTech.com's 2x4 port Matrix DVI A/V Switch includes an IR Remote Control and an additional (external) IR cable sensor that lets you install the switch in a discreet location while maintaining full control. For rackmounted installations, the matrix switch also includes ear-mounts that allow installation in any 19in(w) equipment rack/cabinet.

### Applications

- Demos and tradeshow that include video presentation with multiple inputs and outputs
- In-store product merchandising
- Information kiosks
- Digital Signage

## Features

- Allows two DVI computers to provide video input to display on four different monitors with audio
- Allows you to switch video input signals or toggle video and audio on/off on all four displays
- Cascadable with other switchers, units allow use of one remote control (remote control included)
- Equipped with easy to use front panel selection buttons
- Supports video resolutions up to 1600x1200
- Rack-mountable design enables you to mount this DVI Matrix Switch in a standard 19" rack

## Technical Specifications

Warranty	2 Years
Ports	4
Audio	Yes
Rack-Mountable	Yes
Daisy-Chain	Yes
Connector A	2 - 3.5 mm Mini-Jack (3 Position) Female
Connector A	2 - DVH (29 pin) Female
Connector B	4 - 3.5 mm Mini-Jack (3 Position) Female
Connector B	4 - DVH (29 pin) Female
Maximum Cable Length	16.4 ft [5 m]
Color	Black
Enclosure Type	Aluminum
Product Length	3.8 in [97 mm]
Product Width	8.7 in [220 mm]
Product Height	1.6 in [41 mm]
Product Weight	26.3 oz [744 g]
Output Current	1.5A
Output Voltage	12 DC
Operating Temperature	5 to 40
Storage Temperature	-20 to 60
Shipping (Package) Weight	2.7 lb [1.2 kg]
Included in Package	1 - DVI A/V Matrix Switcher
Included in Package	1 - Set of Ear-Mounts for Rack Mounting
Included in Package	1 - Remote Control
Included in Package	1 - IR External Sensor
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

