

## 8 Port High Resolution VGA Video Switch with Remote

StarTech ID: VS815RVGA



This 8 port VGA Video Switch allows you to select between eight separate VGA video signals for output to a single monitor or projector up to 65m (213ft) away from the video source.

A versatile solution for virtually any environment that requires the ability to switch between VGA displays, the VGA switch supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth.

A perfect solution for situations where VGA input ports are at a premium, the 8 port VGA Video Switch eliminates the hassle of having to swap out connections to your display, and allows you to select your video source at the push of a front panel pushbutton or by using the included remote control.

### Applications and Solutions

- Excellent solution for connecting and switching between multiple PC's to one display.
- Great for use in presentations, tradeshow, conferences, retail, and entertainment applications.

## Features

- Connect to your display at a maximum distance of 65 meters
- Switch between PC's by using the controls on the switcher or the included remote control
- Supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth
- Solid construction in a metal enclosure
- Can be daisy chain

## Technical Specifications

- Warranty: 2 Years
- Bandwidth: 450MHz
- Product Height: 1.65 in [42 mm]
- Product Length: 7.8 in [198 mm]
- Maximum Cable Length: 213.2 ft [65 m]
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Output Current: 1A
- Carton Quantity: 10
- Storage Temperature: -50°C to 70°C (-58°F to 158°F)
- Shipping (Package) Weight: 2.1 lb [0.95 kg]
- Product Width: 2.64 in [67 mm]

