

8 Port High Resolution VGA Video Switch with Remote

StarTech ID: VS815RVGA



This 8 port VGA Video Switch allows you to select between eight separate VGA video signals for output to a single monitor or projector up to 65m (213ft) away from the video source.

A versatile solution for virtually any environment that requires the ability to switch between VGA displays, the VGA switch supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth.

A perfect solution for situations where VGA input ports are at a premium, the 8 port VGA Video Switch eliminates the hassle of having to swap out connections to your display, and allows you to select your video source at the push of a front panel pushbutton or by using the included remote control.

Applications

- Excellent solution for connecting and switching between multiple PC's to one display.
- Great for use in presentations, tradeshow, conferences, retail, and entertainment applications.

Features

- Connect to your display at a maximum distance of 65 meters
- Switch between PC's by using the controls on the switcher or the included remote control
- Supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth
- Solid construction in a metal enclosure
- Can be daisy chain

Technical Specifications

Warranty	2 Years
Ports	8
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Connector Type(s)	8 - VGA (15 pin; High Density D-Sub) Male
Maximum Cable Length	213.2 ft [65 m]
Bandwidth	450MHz
Color	Black
Product Length	7.8 in [198 mm]
Product Width	2.6 in [67 mm]
Product Height	1.7 in [42 mm]
Power Adapter Included	Yes
Output Voltage	5 DC
Output Current	1A
Operating Temperature	05/8/2012eg;C to 405/8/2012eg;C (325/8/2012eg;F to 1045/8/2012eg;F)
Storage Temperature	-505/8/2012eg;C to 705/8/2012eg;C (-585/8/2012eg;F to 1585/8/2012eg;F)
Shipping (Package) Weight	2.1 lb [1 kg]
Included in Package	1 - 8 Port Video Selector
Included in Package	1 - Remote Control
Included in Package	1 - Power Adapter (5V DC, 1A)
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

