

1000 ft Bulk Roll of Blue CMR Cat5e Solid UTP Cable

StarTech ID: WIRC5E350CMR



This Cat5e 350MHz Solid UTP Cable is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000ft bulk roll. The cable features a blue PVC jacket that provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

Applications

- Ideal for network installation at home, office, or educational institution
- CMR rated for use in walls, conduit, ceiling and other vertical applications

Features

- 4-pair unshielded twisted pair (UTP) cable
- Flexible PVC rated jacket
- 24A WG solid bare copper conductor
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC
Industry Standards	Category 5
Industry Standards	CMR
Color	Blue
Wire Gauge	24 AWG
Cable Length	999.7 ft [304.8 m]
Product Length	999.7 ft [304.8 m]
Product Weight	24.5 lb [11.1 kg]
Shipping (Package) Weight	24.5 lb [11.1 kg]
Included in Package	1 - Solid Blue Cat 5E CMR Wire

Certifications, Reports and Compatibility

