

## 500 ft Cat 5e & RG6 Combo Coaxial Cable by the Roll

StarTech ID: WIRC5ERG6CMR



Take care of all your networking and video cabling needs with a single cable product. Our 2-in-1 Cat5e/RG6 cable is the perfect solution for all your high-speed networking, video and cable applications, voice and multimedia applications and much more. We use high-quality shielding to protect the cabling from interference and ensure maximum performance. This 500 ft roll ensures you'll have enough cabling to get the job done while keeping your costs low. With high quality, low cost, and a lifetime warranty, StarTech.com is the professional's choice for cables needs.

A cutting charge applies for requested cable lengths less than a whole roll. Price is per foot.

### Applications and Solutions

- Can be used in home, office and other environments
- CMR rated for use in walls and conduit in ceiling
- Ideal for 10Base-T(IEEE 802.3), 100Base-TX(IEEE 802.3u), 1000Base-TX, 100 Vg AnyLAN(IEEE802.12) and Token Ring (IEEE 802.5)
- Ideal for networking, voice & Multimedia applications, cable and satellite system video distribution as well as for cable modem distribution

## Features

- Copper center conductor and low-loss dielectric minimizes signal loss
- Heavy duty PVC jacket resists abrasion and increases flexibility
- Lifetime Warranty
- Meets or exceeds Cat5e specifications
- Quad shielding provides maximum protection against interference
- Standard RG6 type, 75 Ohm video cable and Cat5e in a flexible PVC jacket

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Impedance: 75 Ohm
- Cable Jacket Type: PVC
- Product Length: 501.84 ft [153 m]
- Carton Quantity: 1
- Cable Shield Type: Quad shielding
- Industry Standards: CMR rated
- Industry Standards: Category 5
- Industry Standards: RG6
- Shipping (Package) Weight: 34.92 lb [15.8 kg]