

## 1000 ft Bulk Roll of CMR RG6 Satellite TV Video Coaxial Cable

StarTech ID: WIRRG6CMR



This standard RG6 type 75 Ohm video cable comes in a durable, yet flexible PVC jacket to protect it from damage.

This 1000 ft roll ensures you'll have enough cabling to get the job done while keeping your costs low.

With high quality, low cost, and a lifetime warranty, StarTech.com is the professional's choice for all your cable needs.

### Applications

- Ideal for cable and satellite system video distribution as well as for cable modem distribution
- Can be used in home, office and other environments
- CMR rated for use in walls, conduit, ceiling and other vertical applications

### Features

- Heavy duty PVC jacket resists abrasion and increases flexibility
- Standard RG6 type, 75 Ohm video cable in a flexible PVC jacket
- Copper center conductor and low-loss dielectric minimizes signal loss
- Lifetime Warranty

### Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	RG6
Impedance	75 Ohm
Color	Black
Wire Gauge	18 AWG
Cable Length	1000 ft [304.9 m]
Shipping (Package) Weight	587.4 oz [16640 g]

### Certifications, Reports and Compatibility

