

Heavy Duty 2-Post Rack - 12U

Product ID: 2POSTRACK12



This 2-post rack stands on your floor or desktop to provide 12U of storage space for EIA-310-D compliant 19" rack-mount devices, such as telecommunication and A/V equipment. The rack creates a robust storage solution, with support for a total load capacity of 160 kg (350 lb.).

Save space and cost, without losing weight capacity

This compact 2-post mounting solution offers a small footprint, and it's engineered to provide exceptional stability, with a total weight capacity of up to 160 kg (350 lb.). The rack fits in virtually any environment, and can be positioned on any surface, such as your floor, desk or table.

Save money, with a cost-effective, compact shipping package

The 2-post server rack comes in a flat-packed box to reduce shipping volume, which also significantly reduces your costs in shipping. The rack is packaged efficiently, so you can easily store it for deployment at a later date.

Hassle-free hardware installation, with tool-less clip nuts

To help make your equipment install easier, this rack includes tool-less clip nuts that seamlessly work with the punched round holes featured on this rack. The tool-less clip nuts provide an easy-to-install nut, unlike square cage nuts which can be a hassle.

The 2POSTRACK12 is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

- Use this cabinet to house your A/V equipment in a restaurant or bar, where space may be limited
- Rack-mount the equipment in your repair center or technology shop
- House equipment in audio-video editing rooms, or radio and television broadcast studios

Features

- Save space with a compact 2-post rack solution
- Get heavy-duty weight capacity up to 350 lb. (160 kg)
- Reduce your shipping costs with a flat-packed rack
- Easy equipment installation with tool-less clip nuts
- Maximize compatibility with EIA-310-D compliance
- 12U of rack space

Hardware	Warranty	Lifetime
	Additional Required Tools	Phillips Screwdriver
	Cable Management	No
	Casters	No
	Frame Type	Open Frame
	Industry Standards	EIA-310-D
		EIA RS310-D
	Ladder Offset	0.2 in [5 mm]
	Ladder Type	L-Shape
	Mounting Holes	Circle
	Mounting Options	Front Mount
	Number and Type of Included Cage Nuts	36 - 10-32
	Rack Type	2-Post
	Tools Included	No
	U Height	12U
U Markings	No	
Wallmountable	No	
Performance	Weight Capacity (Stationary)	353.6 lb [160 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Internal Width	17.8 in [451 mm]
	Product Height	24.1 in [613 mm]
	Product Length	12 in [306 mm]
	Product Weight	14.7 lb [6.7 kg]
	Product Width	20.4 in [518 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	17 lb [7.7 kg]
What's in the Box	Included in Package	1 - right bracket 1 - left bracket

- 1 - top bracket
- 1 - bottom bracket
- 4 - rubber feet
- 12 - 10-32 Phillips screws
- 36 - 10-32 mounting screws
- 36 - clip nuts
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.