

2-Post Server Rack with Casters - 42U

Product ID: 2POSTRACK42



Store your server, network and telecommunications equipment in this sturdy 42U rack. With a 2-post design, the rack saves floor space and its dual-post, open-depth design makes it broadly compatible with longer equipment.

Maximum portability

The 2-post rack features four swiveling casters, so you can easily move it around in your server room, office or studio. It's easy to reposition or relocate the rack in order to connect your rack-mounted equipment to other devices throughout your workspace.

High durability

The durable dual-post server rack is made of heavy-gauge steel, instead of aluminum, to ensure a stable installation platform. The rack supports a static loading capacity of up to 600 lb. (272 kg), and it's compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), to provide a stable platform that eliminates the need for concrete mounting kits.

Wide compatibility

You can easily mount your ANSI/EIA RS-310-D compliant network equipment to the rack without using additional hardware. It features square mounting holes on the frame and a universal design that's compatible with most rack equipment.

The 2POSTRACK42 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use in your server room or any location where telecommunication and networking equipment needs to be housed
- Create a portable video editing and production rack that you can move around your studio to interface with different equipment

Features

- Maximum portability with four swiveling casters for easy transportation
- Widely compatible with most rack-mountable equipment with square mounting holes and a 2-post open frame design
- Superior durability and stability with full-steel construction
- 42U of mounting space
- Mount standard networking equipment using standard cage nuts and screws
- Easy assembly at the point of installation for rapid deployment

Hardware	Warranty	2 Years
	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	No
	Cable Management	No
	Casters	Included
	Fan(s)	No
	Frame Type	Open Frame
	Industry Standards	EIA-310-D DIN41491 Part I DIN41491 Part VII EIA RS310-D GB/T3047.2-92 IEC297-2
	Ladder Offset	0.8 in [20 mm]
	Ladder Type	C-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	32 - M6
	Rack Type	2-Post
	Tools Included	Yes
	U Height	42U
	U Markings	Yes
	Wallmountable	No
Performance	Weight Capacity (Stationary)	663 lb [300 kg]
Special Notes / Requirements	Note	32 M6 cage nuts, 32 M6 rack screws, 20 M6 assembly nuts, 30 M6 assembly screws, 2 casters, 2 locking casters, 16 M6 caster screws, 32 washers, 1 hex key
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Height with Casters	81.9 in [207.9 cm]
	Product Height	79.1 in [2008 mm]
	Product Length	23.6 in [600 mm]

	Product Weight	52.1 lb [23.6 kg]
	Product Width	23.5 in [597 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	66.2 lb [29.9 kg]
What's in the Box	Included in Package	2 - bottom supporting beams
		2 - vertical rails
		2 - horizontal rails
		2 - angle support beams
		2 - 2" heavy-duty casters
		2 - 2" heavy-duty locking casters
		30 - M6 screws
		20 - M6 nuts
		16 - M6 caster screws
		32 - M6 cage nuts
		32 - M6 rack screws
		32 - plastic washers
		1 - hex key 4mm
1 - quick install guide		

Product appearance and specifications are subject to change without notice.