

## 2-Post Server Rack with Casters - 42U

Product ID: 2POSTRACK42



Store your server, network and telecommunications equipment in this sturdy 42U rack. With a 2-post design, the rack saves floor space and its dual-post, open-depth design makes it broadly compatible with longer equipment.

### Maximum portability

The 2-post rack features four swiveling casters, so you can easily move it around in your server room, office or studio. It's easy to reposition or relocate the rack in order to connect your rack-mounted equipment to other devices throughout your workspace.

### High durability

The durable dual-post server rack is made of heavy-gauge steel, instead of aluminum, to ensure a stable installation platform. The rack supports a static loading capacity of up to 600 lb. (272 kg), and it's compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), to provide a stable platform that eliminates the need for concrete mounting kits.

## **Wide compatibility**

You can easily mount your ANSI/EIA RS-310-D compliant network equipment to the rack without using additional hardware. It features square mounting holes on the frame and a universal design that's compatible with most rack equipment.

The 2POSTRACK42 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Use in your server room or any location where telecommunication and networking equipment needs to be housed
- Create a portable video editing and production rack that you can move around your studio to interface with different equipment

### Features

- Maximum portability with four swiveling casters for easy transportation
- Widely compatible with most rack-mountable equipment with square mounting holes and a 2-post open frame design
- Superior durability and stability with full-steel construction
- 42U of mounting space
- Mount standard networking equipment using standard cage nuts and screws
- Easy assembly at the point of installation for rapid deployment

<b>Hardware</b>	Warranty	2 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	C-Shape
	Rack Type	2-Post
	Special Features	Casters (Included)
		Easy Assembly
		U-Markings
U Height	42U	
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	663 lb [300 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Product Height	79.1 in [200.8 cm]
	Product Height with Casters	81.9 in [207.9 cm]
	Product Length	23.6 in [60 cm]
	Product Width	23.5 in [59.7 cm]
	Weight of Product	52.1 lb [23.6 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Height	6.7 in [17.1 cm]
	Package Length	6.7 ft [2.1 m]
	Package Width	8.5 in [21.7 cm]
	Shipping (Package) Weight	66.2 lb [29.9 kg]
<b>What's in the Box</b>	Included in Package	2 - Bottom Supporting Beams
		2 - Vertical Rails
		2 - Horizontal Rails
		2 - Angle Support Beams
		2 - 2" Heavy-Duty Casters
		2 - 2" Heavy-Duty Locking Casters

- 30 - M6 Screws
- 20 - M6 Nuts
- 16 - M6 Caster Screws
- 32 - M6 Cage Nuts
- 32 - M6 Rack Screws
- 32 - Plastic Washers
- 1 - Hex Key 4mm
- 1 - Quick Install Guide

---

Product appearance and specifications are subject to change without notice.