

3.5in Front Bay 22-in-1 USB 2.0 Multi Media Memory Card Reader - Black

Product ID: 35FCREADBK2



This 3.5-inch Front Bay Mount 22-in-1 Multimedia Card Reader allows for quick and easy access to the most popular flash card formats, from almost any desktop computer with a 3.5-inch bay opening.

With support for Compact Flash (CF type I/II), Secure Digital (SD/miniSD/microSD/SDHC/SDXC), MultiMediaCard (MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC), MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture cards, this reader is ready to handle the memory cards from virtually any portable device from cameras to music players.

Certifications, Reports and Compatibility



Applications

- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

Features

- Supports CompactFlash type I/II, SD/miniSD/microSD/SDHC/SDXC, MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC, MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture card
- Front panel USB port for convenient access
- Fits into any external 3.5in drive bay
- High Speed USB 2.0 compliant, with support for data transfer rates up to 480 Mbps
- Powered directly from the USB connection
- Durable metal enclosure
- Power/Activity LED indicator
- Connects internally to a 9-pin USB motherboard header via included cable
- Plug and Play compatible

	Warranty	2 Years
Hardware	Chipset ID	ITE - 1336
Performance	Memory Media Type	CF (Compact Flash I/II Card) HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card) HS-MS (High Speed Memory Stick) M2 (Memory Stick Micro) Memory Stick microSDHC (Micro Secure Digital High Capacity) Mini-SD, Micro-SD (Mini/Micro Secure Digital) MS Duo, MS Pro Duo, MS Pro-HG Duo Multi Media Card RS-MMC (Reduced Size Multimedia Card) SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity) xD (Extreme Digital) Picture Card
Connector(s)	Connector Type(s) External Ports	1 - IDC (10 pin, Motherboard Header) Female 1 - CompactFlash (50 pin) Slot 1 - Memory Stick / Memory Stick Pro Slot Female 1 - Memory Stick Micro (M2) Slot Female 1 - MiniSD / MicroSD / MMC Slot Female 1 - SD / MMC Slot Female 1 - USB Type-A (4 pin) USB 2.0 Female 1 - xD-Picture Card Slot Female
Software	OS Compatibility	Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8 (32/64-bit) Linux kernel 2.4.x or later
Special Notes / Requirements	System and Cable Requirements	Available internal 9-pin USB motherboard header
Indicators	LED Indicators	1 - Power/Activity
Power	Power Source	USB-Powered

Environmental	Humidity	15~85%
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 125°C (-40°F to 257°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	1 in [25 mm]
	Product Length	5.1 in [130 mm]
	Product Weight	5.8 oz [164 g]
	Product Width	4.1 in [105 mm]
Packaging Information	Shipping (Package) Weight	7.8 oz [220 g]
What's in the Box	Included in Package	1 - Card Reader
		1 - 9-pin IDC USB cable
		1 - Bag of Mounting Screws
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.