

USB 3.0 Internal Multi-Card Reader with UHS-II Support

Product ID: 35FCREADBU3



Now, you can transfer large files like photos and 4K video, back up files or offload data, to and from your memory cards, at speeds like never before. This USB 3.0 internal multi-card reader supports UHS-II to greatly enhance your file transfer rates. The card reader supports High Capacity/eXtended Capacity cards and most standard memory cards, including SecureDigital®, Compact Flash®, Memory Stick® and micro SD cards. It also enables concurrent downloads. Fast speed and wide compatibility make this multi-card reader an ideal solution for photo kiosks or photo labs, and desktop computers.

The card reader is USB powered so there's no external power or battery required. Front USB access lets you connect USB devices easily.

Transfer files quickly and easily

With support of UHS-II cards, the multi-card reader lets you transfer large files to and from your memory cards at speeds of up to 312 MB/s, saving you time on data offloads of 4K, full HD and 3D videos.

Using a USB 3.0 connection, also known as USB 3.1 Gen 1, the card reader supports fast file transfer speeds of up to 5 Gbps, enabling you to leverage the increased capabilities of new, higher performing memory cards.

Access multiple cards - at the same time

Save time with concurrent downloads. This 5-slot multi-card reader design allows you to access up to four memory cards simultaneously for fast and easy file transfers.

Read most standard memory cards from a single card reader

The USB 3.0 multi-card reader works with most standard memory cards, including:

- Secure Digital (Standard Card, HC card, XC card, MMC, Mini SD with adapter)
- Micro SD (Standard card, HC card, XC card)
- Compact Flash (CF I or II, CF 6.0)
- Memory Stick (Standard, Pro, Duo, Pro Duo, Pro-HG, XC, Micro MS with adapter)

The 35FCREADB3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Provide read/write access to a wide range of memory cards, ideal for photo labs and kiosks
- Read and copy high-res image files quickly and efficiently, an effective solution for medical units, school systems and business applications
- Back-up and copy data, photos and video from your memory cards to your home computer, or from your computer to a memory card

Features

- USB 3.0 (5 Gbps) multi-card reader transfers video, images and files at ultra-fast speeds
- Supports UHS-II with transfer speeds of up to 312 MB/s
- Multi-card reading and writing for most standard cards, including: SecureDigital®, Micro SD, Compact Flash®, Memory Stick® and more
- High Capacity/eXtended Capacity support
- 5-slot design allows simultaneous file transfers for up to 4 memory cards
- Powered directly from the USB 3.0 port with front USB access
- Includes an integrated USB IDC cable
- No driver or software installation required

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	Realtek - RTS5321
	Interface	USB 3.0
	Number of Drives	2
Performance	Maximum Data Transfer Rate	5 Gbps
	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
		SDXC (Secure Digital eXtended Capacity)
		SDHC (Secure Digital High Capacity)
		Mini-SD, Micro-SD (Mini/Micro Secure Digital)
		microSDHC (Micro Secure Digital High Capacity)
		CF (Compact Flash I/II Card)
		HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)
		MS/MS Pro (Memory Stick/Memory Stick Pro)
		MS Duo, MS Pro Duo, MS Pro-HG Duo
HS-MS (High Speed Memory Stick)		
MSXC (Memory Stick eXtended Capacity)		
MS Micro (Memory Stick Micro)		
MS MG (Memory Stick w/ MagicGate)		
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Drive Connectors	2 - SD / MMC Slot
		1 - Memory Stick / Memory Stick Pro Slot
		1 - MicroSD
		1 - CompactFlash (50 pin) Slot
		1 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed)
	Host Connectors	1 - IDC (20 pin, USB 3.0, Motherboard Header)
Software	OS Compatibility	OS independent; No software or drivers required
Indicators	LED Indicators	2 - Power and Access
Environmental	Humidity	15% ~ 85% RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)

Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	0.9 in [24 mm]
	Product Length	4.6 in [118 mm]
	Product Weight	8.8 oz [250 g]
	Product Width	3.9 in [100 mm]
Packaging Information	Shipping (Package) Weight	11 oz [312 g]
What's in the Box	Included in Package	1 - USB 3.0 memory card reader
		4 - mounting screws
		1 - quick start guide

Product appearance and specifications are subject to change without notice.