

12U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet

Product ID: 4POSTRACK12



The 4POSTRACK12 12U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet provides a durable, open air housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation. The 12U open frame rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For added versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 12U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Useful for point of sale applications, specifically mounting equipment under the check-out counter
- Mounting equipment under a desk/workspace
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Store your servers, network and telecommunications equipment in this 12U open-frame rack
- 12U Open Frame Rack with a weight capacity of 1000 lb (452.5 kg)
- TAA compliant for GSA Schedule purchases
- Flat packed for easy shipping
- Pre-drilled base and unobstructed ventilation
- Heavy gauge adjustable mounting rails ensure broad equipment compatibility

Hardware	Warranty	Lifetime
	Adjustable Mounting Rails	Yes
	Cable Management	No
	Casters	Optional
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA-310-D EIA RS310-C
	Ladder Type	C-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	32 - M5
	Rack Type	4-Post
	Tools Included	Yes
	U Height	12U
	U Markings	No
Wallmountable	No	
Performance	Weight Capacity (Stationary)	1000 lb [452.5 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Height with Casters	28.3 in [719 mm]
	Internal Height	21.1 in [536.6 mm]
	Maximum Mounting Depth	39.4 in [1000 mm]
	Minimum Mounting Depth	18.3 in [465 mm]
	Product Height	25.5 in [648 mm]
	Product Length	31.5 in [800 mm]
	Product Weight	63.9 lb [28.9 kg]
	Product Width	22.5 in [572 mm]
Rail Thickness	0.1 in [2 mm]	
Packaging Information	Flat Pack (Assembly Required)	Yes

	Shipping (Package) Weight	70 lb [31.7 kg]
What's in the Box	Included in Package	1 - 12 U Open Rack 1 - Assembly Kit (Screw, wrench, caps) 1 - Package of Cab screws and Cage nuts(24 each) 1 - Assembly Instructions

Product appearance and specifications are subject to change without notice.