

# 12U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

### Features

- 12U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Adjustable Mounting Rails	Yes
	Cable Management	Yes D-Rings
	Casters	Included
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Front Door Key Lock	No
	Industry Standards	EIA-310-D
		DIN 41494
		EIA/ECA-310-E
		IEC 60297-3-100
	Ladder Offset	0.5 in [12 mm]
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	24 - M6
	Rack Type	4-Post
	Tools Included	Yes
	U Height	12U
	U Markings	Yes
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Height with Casters	28 in [710 mm]
	Internal Height	21.2 in [538 mm]
	Maximum Mounting Depth	40 in [1017 mm]
	Minimum Mounting Depth	22 in [560 mm]
	Product Height	25.1 in [638 mm]
	Product Length	23.2 in [590 mm]
Product Weight	50.3 lb [22.7 kg]	

	Product Width	23.6 in [600 mm]
	Rail Thickness	0.1 in [2 mm]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	58.2 lb [26.3 kg]
<b>What's in the Box</b>	Included in Package	<ul style="list-style-type: none"> <li>2 - Left Vertical Rail</li> <li>2 - Right Vertical Rail</li> <li>2 - Base Bracket</li> <li>8 - Corner Section</li> <li>4 - Center Section</li> <li>2 - Top Bracket</li> <li>48 - M8 Bolt</li> <li>48 - M8 Washer</li> <li>1 - M8 (13mm) Wrench</li> <li>1 - M6 (10mm) Wrench</li> <li>1 - Phillips Screwdriver</li> <li>24 - M6 Cage Nut</li> <li>24 - PVC Cup Washer</li> <li>24 - M6 Phillips Head Screw</li> <li>4 - Cable Management Hook</li> <li>4 - Hook Mounting Screw</li> <li>4 - Casters</li> <li>4 - Leveling Feet</li> <li>16 - M6 Screw</li> <li>16 - M6 Flat Washer</li> <li>16 - M6 Flange Nut</li> <li>4 - Grounding Wires</li> </ul>

Product appearance and specifications are subject to change without notice.