

25U Adjustable Depth 4 Post Open Frame Server Rack Cabinet

Product ID: 4POSTRACK25



The 4POSTRACK25 25U 4 Post Open Frame Rack provides a durable, open air housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server rack features heavy gauge mounting rails to ensure a stable installation platform, with support for mounting depth adjustment (23.5 - 31.5in), giving you the flexibility to fit your rack-mounted equipment.

This 25U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the rack is flat-packed to reduce shipping costs and simplify handling.

For added versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the rack, making it easier to re-position the cabinet/rack as needed for future uses.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- 25U Open frame design
- Adjustable mounting depth from 23.5 - 31.5in
- Supports a weight capacity of up to 994.5lbs (450kg)
- Heavy gauge mounting rails
- Pre-drilled holes to secure the rack directly to the floor
- Unobstructed ventilation and cable routing
- Flat-packed for easy shipping
- TAA compliant for GSA Schedule purchases

Hardware	Warranty	Lifetime
	Adjustable Mounting Rails	Yes
	Cable Management	No
	Casters	Optional
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA-310-D
	Ladder Type	C-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	62 - M5
	Rack Type	4-Post
	Tools Included	Yes
	U Height	25U
	U Markings	No
Wallmountable	No	
Performance	Weight Capacity (Stationary)	994.5 lb [450 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Height with Casters	51 in [1296 mm]
	Maximum Mounting Depth	39.3 in [997 mm]
	Minimum Mounting Depth	18.3 in [466 mm]
	Product Height	48.2 in [1225 mm]
	Product Length	23.6 in [600 mm]
	Product Weight	84.2 lb [38.1 kg]
	Product Width	22.5 in [571 mm]
Rail Thickness	0.1 in [2 mm]	
Packaging Information	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	92.2 lb [41.7 kg]
What's in the Box	Included in Package	2 - Front/Rear Frames

- 2 - Floor Plates
- 6 - Adjustable Horizontal Arms
- 2 - Floor Mounting Brackets
- 1 - M8 Hex (Allen) key
- 8 - M8x25 Hex Socket Screws
- 42 - M5x15 Truss Head Screws
- 16 - Bushing Caps
- 24 - Cabinet Screws
- 24 - Cage Nuts

Product appearance and specifications are subject to change without notice.