

# 25U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK25U



The 4POSTRACK25U 25U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 25U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Certifications, Reports and Compatibility**



### **Applications**

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

### **Features**

- 25U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Adjustable Mounting Rails	Yes
	Adjustable Size of Built-in Leveling Feet	100 mm [3.94 in]
	Cable Management	Yes Hooks
	Casters	Included
	Fan(s)	No
	Frame Type	Open Frame
	Industry Standards	EIA-310-D
	Ladder Offset	0.6 in [15 mm]
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	32 - M6
	Rack Type	4-Post
	Style	Floor-Standing
	Tools Included	Yes
	U Height	25U
	U Markings	Yes
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Height with Casters	50.8 in [1290 mm]
	Internal Height	43.9 in [1115.8 mm]
	Maximum Mounting Depth	40 in [1017 mm]
	Minimum Mounting Depth	22 in [560 mm]
	Product Height	47.8 in [1213 mm]
	Product Length	41.3 in [1048 mm]
	Product Weight	72.9 lb [33 kg]
	Product Width	23.8 in [604 mm]
Rail Thickness	0.1 in [2 mm]	

<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	77.4 lb [35 kg]
<b>What's in the Box</b>	Included in Package	2 - Left Vertical Rail
		2 - Right Vertical Rail
		2 - Base Bracket
		8 - Corner Section
		4 - Center Section
		2 - Top Bracket
		48 - M8 Bolt
		48 - M8 Washer
		1 - M8 (13mm) Wrench
		1 - M6 (10mm) Wrench
		1 - Phillips Screwdriver
		32 - M6 Cage Nut
		32 - PVC Cup Washer
		32 - M6 Phillips Head Screw
		12 - Cable Management Hook
12 - Hook Mounting Screw		
4 - Casters		
4 - Leveling Feet		
16 - M6 Screw		
16 - M6 Flat Washer		
16 - M6 Flange Nut		
4 - Grounding Wires		

Product appearance and specifications are subject to change without notice.