

## 42U Adjustable Depth Open Frame 4 Post Server Rack Cabinet - Flat Pack w/ Casters, Levelers and Cable Management Hooks

Product ID: 4POSTRACK42



The 4POSTRACK42 42U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 42U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1320lbs (600kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete rack solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securing the rack to the floor if needed, providing you with many options to customize the rack to fit your environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

### Features

- 42U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1320lbs (600kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Adjustable Mounting Rails	Yes
	Cable Management	Yes D-Rings
	Casters	Included
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Front Door Key Lock	No
	Industry Standards	EIA-310-D
		DIN 41494
		EIA/ECA-310-E
		IEC 60297-3-100
	Ladder Offset	0.6 in [15 mm]
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	50 - M6
	Rack Type	4-Post
Side Panel(s) Key Lock	No	
Tools Included	Yes	
U Height	42U	
U Markings	Yes	
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	1326 lb [600 kg]
<b>Special Notes / Requirements</b>	<b>Note</b>	4x casters, 18x M6 caster bolts, 18x M6 caster flange nuts, 18x M6 caster washers, 50x M8 assembly bolts, 50 M8 assembly washers, 50 PVC cup washer, 50 M6 Cage Nuts, 50x M6 phillips bolts, 4x grounding wires, 4x leveling feet, Phillips screwdriver, M6 wrench, M8 wrench, 4x M6 grounding wire bolts (short), 4x M6 grounding wire lock washers, 24x cable clips, 24x cable clip screws.
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Height with Casters	80.3 in [204 cm]

	Internal Height	73.7 in [1871.5 mm]
	Maximum Mounting Depth	40 in [1017 mm]
	Minimum Mounting Depth	22 in [560 mm]
	Product Height	77.6 in [1970 mm]
	Product Length	41.3 in [1048 mm]
	Product Weight	85.1 lb [38.5 kg]
	Product Width	23.8 in [604 mm]
	Rail Thickness	0.1 in [2 mm]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	90.6 lb [41 kg]
<b>What's in the Box</b>	Included in Package	2 - Left Vertical Rail
		2 - Right Vertical Rail
		2 - Base Bracket
		8 - Corner Section
		4 - Center Section
		2 - Top Bracket
		48 - M8 Bolt
		48 - M8 Washer
		1 - M6 (10mm) Wrench
		1 - M8 (13mm) Wrench
		1 - Phillips Screwdriver
		50 - M6 Cage Nut
		50 - PVC Cup Washer
		50 - M6 Phillips Head Screw
		24 - Cable Management Hook
	24 - Hook Mounting Screw	
	4 - Casters	
	4 - Leveling Feet	
	16 - M6 Screw	
	16 - M6 Flat Washer	
	16 - M6 Flange Nut	

4 - Grounding Wires

Product appearance and specifications are subject to change without notice.