

# 42U Adjustable 4 Post Open Server Equipment Rack Cabinet

Product ID: 4POSTRACKBK



StarTech.com's DuraRak 42U Adjustable 4 Post Open Server Rack offers a solid, versatile solution for mounting servers and other networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This full size (42U) rack offers adjustable posts for maximum flexibility, and an open frame design with heavy gauge mounting rails to ensure exceptional structural stability.

To ensure broad compatibility, the 42U rack features an industry standard design for compatibility with equipment from popular manufacturers.

A cost-effective solution, the rack is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty, plus the rack is flat-packed for easier handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed to the bottom of the 42U server rack.



### Certifications, Reports and Compatibility



### Applications

- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

### Features

- Open frame design with heavy gauge mounting rails provides exceptional structural stability
- Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature
- TAA compliant for GSA Schedule purchases
- Easily route, manage and access your equipment cables without any obstruction
- Adjustable mounting rails ensure compatibility with many rack mount equipment
- Heavy-duty base with holes allow you to bolt the server rack to the floor when mounting heavy rack mount equipment

<b>Hardware</b>	Warranty	Lifetime
	Additional Required Tools	Phillips Screwdriver Cage Nut Tool
	Adjustable Mounting Rails	Yes
	Cable Management	No
	Casters	No
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA/ECA-310-E
	Ladder Type	C-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	92 - M5
	Rack Type	4-Post
	Tools Included	No
	U Height	42U
	U Markings	No
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	994.5 lb [450 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Internal Depth	18.4 in [468 mm]
	Internal Height	73.6 in [1870 mm]
	Internal Width	17.7 in [449 mm]
	Maximum Mounting Depth	39.2 in [995 mm]
	Minimum Mounting Depth	22.9 in [582 mm]
	Product Height	78 in [1980 mm]
	Product Length	39.2 in [995 mm]
	Product Weight	102.2 lb [46.3 kg]
Product Width	22.4 in [570 mm]	
Rail Thickness	0.1 in [2 mm]	

<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	112.3 lb [50.8 kg]
<b>What's in the Box</b>	Included in Package	2 - Front/Rear Frame
		2 - Floor Plates
		6 - Adjustable Horizontal Arm
		2 - Floor Mounting Brackets
		1 - M8 Hex (Allen) key
		8 - M8x25 Hex Socket Screws
		42 - M5x15 Truss Head Screws
		16 - Bushing Caps
24 - Cabinet Screws		
		24 - Cage Nuts

Product appearance and specifications are subject to change without notice.