

Refurbished 12U 4 Post Open Frame Rack with Adjustable Posts & Casters

Product ID: 4POSTRK12AR



The 4POSTRACK12A Open Frame Rack offers a durable, yet flexible open-air housing for rack-mount servers and networking equipment. The rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform with two adjustable posts for variable mounting depths.

Providing a universal design that's compatible with equipment from popular manufacturers, this EIA-RS-310C compliant open rack ships flat packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, this 12U rack ships with 4 swiveling casters and has a total height of less than 26" (661mm) which allows the rack to be rolled under most desks or work benches with little effort.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

Certifications, Reports and Compatibility



Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Useful for point of sale applications, specifically mounting equipment under the check-out counter
- Suitable for rackmount equipment where security at the rack level is not required
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Mounting equipment under a desk/workspace
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Swivel Casters included
- Two Adjustable Rails for variable mounting depths
- Open frame design easy access and greater air flow
- Shipped as a flat pack for easier handling
- Less than 3ft tall, perfect for rolling under desks or benches
- Heavy gauge mounting rails

Hardware	Warranty	0 Years
	Casters	Included
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA RS310-C
	Rack Type	4-Post
	U Height	12U
	Wallmountable	No
Performance	Weight Capacity (Stationary)	596.7 lb [270 kg]
Physical Characteristics	Color	Black
	External Depth	35.9 in [913 mm]
	External Height	23 in [585 mm]
	External Width	21 in [534 mm]
	Height with Casters	25.9 in [658 mm]
	Internal Height	21 in [534 mm]
	Internal Width	17.8 in [451 mm]
	Maximum Mounting Depth	35.9 in [913 mm]
	Product Weight	17.7 lb [8 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Shipping (Package) Weight	20.8 lb [9.4 kg]
What's in the Box	Included in Package	2 - Front/Read Frame 4 - Assembly Post 2 - Adjustable Rails 4 - Casters 1 - Pack of M6 Cage Nuts and Cab Screws (16 each) 16 - KEP Nuts 52 - 1/4" Washers 52 - 1/4-20 x 12 Hex Bolts

Product appearance and specifications are subject to change without notice.