

Stereo RCA to SPDIF Digital Coaxial and Toslink Optical Audio Converter

Product ID: AA2SPDIF



The AA2SPDIF Stereo RCA to SPDIF Digital Coaxial and Toslink Audio Converter lets you convert or split your analog stereo audio into 2-channel Digital Coaxial and Toslink output signals.

Perfect for many home and professional audio applications, this RCA to digital audio converter saves the cost of upgrading equipment for compatible connections, by offering a separate Digital Coax and Toslink output. For added versatility, the device can also function as an audio splitter using the digital coax and Toslink outputs simultaneously. The converter features a small form factor design that makes it suitable for installation into virtually any location regardless of space constraints, while still providing a lossless audio signal at distances up to 5 meters (15 feet). Plus, the converter supports plug-and-play installation saving you time and hassle.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Run a Toslink cable to one receiver and a digital coaxial cable to another receiver
- Connect older DVD Players, VCRs and Game Consoles to new home theater receivers
- Convert or extend your analog audio input into a digital format, without signal or quality loss

Features

- Accepts RCA Stereo audio input
- Outputs Toslink, Digital Coax (SPDIF), or both
- Compact form factor
- Easy to install and use
- Supports uncompressed 2-channel LPCM (Linear Pulse Code Modulation) digital audio signal output
- Supports output sampling rate at 48 KHz

Hårdvara	Warranty	2 Years
	AV-ingång	Audio RCA
	AV-utgång	Digital Coaxial Toslink
Prestanda	Audio-specifikationer	2 channel (stereo) supported
	Maximal kabellängd	16.4 ft [5 m]
Kontakt(er)	Kontakttyp(er)	1 - Digital koaxial audio (RCA) Hona Output 1 - Toslink (SPDIF, optisk) Hona Output 2 - Stereoaudio (2 x RCA) Hona Input
Ström	Kontakttyp	M
	Polaritet på mittpol	Positiv
	Power Source	AC-adapter medföljer
	Strömförbrukning	1.8
	Utspänning	5 DC
	Utström	0.36A
Miljö	Drifttemperatur	0°C to 48°C (32°F to 118°F)
Utseende	Färg	Vit
	Kabinettyp	Av plast
	Produktbredd	1.8 in [45.5 mm]
	Produkt höjd	0.9 in [23.5 mm]
	Produktlängd	2.2 in [57 mm]
	Produktvikt	1.1 oz [30 g]
Förpackning	Fraktvikt (förpackning)	1 lb [0.5 kg]
Vad det är i lådan	Ingår i paketet	1 - analog RCA to digital coax/toslink converter 1 - universal power adapter (NA, EU, UK, ANZ) 1 - instruction manual

Product appearance and specifications are subject to change without notice.