

1U Adjustable Mounting Depth Vented Rack Mount Shelf - Heavy Duty Fixed Rack Shelf - 250lbs / 113kg

Product ID: ADJSHELFHDV



The ADJSHELFHDV 1U Adjustable Heavy Duty Vented Rack Mount Shelf lets you add a high-capacity, adjustable 1U shelf to virtually any standard 19-inch server rack or cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This heavy duty rackmount shelf can be adjusted from 19.5in to 38in (mounting depth) to fit your rack, while the vented design improves air flow and help to lower temperatures in the rack. Constructed using 1.2mm SPCC commercial grade cold-rolled steel, providing the ability to hold up to 113kg (250lbs) of equipment - a durable solution for storing large, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Adding a storage shelf to shallow depth network switches/equipment racks
- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- 1U Heavy Duty Adjustable Vented Rackmount Shelf
- Fits all standard 19" server racks
- TAA compliant for GSA Schedule purchases
- Adjustable mounting depth from 19.5in to 38in
- Holds up to 113kg (250lbs)
- SPCC 1.2mm Cold-rolled steel construction

Hardware	Warranty	Lifetime
	Cable Management	No
	Frame Type	Steel
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount (Front and Rear)
	U Height	1U
Performance	Weight Capacity (Stationary)	250 lb [113.1 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Maximum Mounting Depth	38.3 in [974 mm]
	Minimum Mounting Depth	19.5 in [495 mm]
	Product Weight	11.9 lb [5.4 kg]
	Rail Thickness	0 in [1.2 mm]
Packaging Information	Shipping (Package) Weight	15.6 lb [7.1 kg]
What's in the Box	Included in Package	1 - 1U High Cap Adjustable Rack Shelf
		2 - Front Mounting Brackets
		2 - Rear Mounting Brackets
		8 - M5 Panel Screws
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.