

Dual-Monitor Stand - Horizontal - Black

Product ID: ARMBARDUO



Increase your productivity and free up desk space with this dual-monitor stand. The free-standing mount lets you install two displays up to 24", side by side, on a single base that you can place in virtually any workspace. The black finish complements your office decor.



Enhance Productivity with a Dual-Monitor Workstation

Set up a dual-monitor workstation with this VESA monitor stand (75x75, 100x100 mm) to multitask faster and boost your productivity. Compare and edit files on two screens with ease. Rotate your monitors 360 degrees for portrait or landscape viewing.

Free Up Desk Space with the Low-Profile Base

Maximize the surface area on your desk with the twin-monitor stand. Its crossbar design makes it easy to mount two flat-panel displays. The monitor stand features a flat, low-profile back so you can position your displays against an office wall or cubicle wall to free up space.

Optimum Viewing

The crossbar design of the dual-monitor stand keeps your monitors perfectly aligned for comfortable viewing. You can customize the positioning of your displays with +/-15 degree tilt. You can also adjust the height of the monitors along the pole, up to 15.9" (40.5 cm).

A Stable Platform with Versatile Use

The robust steel and aluminum monitor stand provides a stable setup for your workstation. The sturdy platform also allows flexible use as a temporary setup, for example, to make presentations in the boardroom.

ARMBARDUO is backed by a 5-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add two monitors to your work station to complete your tasks quicker
- Maximize desk space by mounting both of your monitors on a single base
- Low-profile base with attractive black finish works well in offices or cubicles

Features

- Enhance productivity and free up space by mounting two monitors up to 24"
- Low-profile base, with attractive black finish, sits closely to your office or cubicle wall
- Free-standing monitor stand with crossbar design keeps monitors aligned
- Easy height adjustment along the pole, and +/-15 degree tilt for customized viewing
- Steel and aluminum stand supports VESA 75x75, 100x100, and a weight capacity of 18 lb. (8 kg) per monitor

Hardware	Warranty	5 Years
	# of Displays Supported	2
	Articulating	No
	Mounting Options	Desktop Stand
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Height Adjustment	Yes
	Maximum Display Size	24in
	Maximum Height	15.9 in [405 mm]
	Swivel / Pivot	360° at each display
	Tilt	+/-15
	Weight Capacity (Per Display)	17.7 lb [8 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel, Aluminum and Plastic
	Product Height	16.1 in [410 mm]
	Product Length	37.4 in [950 mm]
	Product Weight	13.6 lb [6.2 kg]
	Product Width	7.1 in [180 mm]
Packaging Information	Shipping (Package) Weight	16.4 lb [7.4 kg]
What's in the Box	Included in Package	1 - pole 1 - baseplate 3 - M6x15 screws 1 - cable-management clip (pole) 1 - pole cap 1 - height-adjustment ring 1 - crossbar 2 - VESA monitor mounts 8 - M4x12 screws 8 - M4x30 screws

- 8 - plastic spacers
- 1 - allen wrench (3mm)
- 1 - allen wrench (4mm)
- 2 - cable-management clips (crossbar)
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.