

## Desk Mount Dual Monitor Arm - Articulating - Premium

Product ID: ARMDUALPS



Create an ergonomic workspace with this premium desk-mount dual monitor arm, for monitors up to 27" each. The two articulating monitor arms with dual-swivel action offer a wide range of motion side to side. The attractive silver finish enhances the aesthetics of your workspace.



### Enjoy a Wide Range of Motion to Work in Comfort

The dual articulating monitor arms offer a wide range of motion on several axes. It provides effortless motion to adjust the position of your monitors.



## Sleek and Stable Aluminum Design

The robust aluminum design provides stable support for your monitors. The computer-monitor desk mount supports two VESA mount monitors (75x75, 100x100) with a weight capacity of up to 22 lb. (10 kg) per display. The cable-management channel helps to keep your workstation neat and tidy.

## Adjust your Viewing Angle

Share your screen with ease. The double monitor mount offers a full +180-degree / -180-degree pan, to move your screen left or right. It tilts freely +90 / -15 degrees to adjust the angle up or down. Rotate your screens for landscape or portrait viewing.

## Height Adjustment

Work in comfort. This height-adjustable monitor mount lets you raise or lower the monitor arms along the pole, with a range of up to 6.3" (160 mm)

## Tool-less Assembly

The fully assembled desk clamp and pole, plus quick slide-and-click connections, ensure easy assembly. It also saves time when setting up multiple units. The dual-screen mount gives you the option of desk clamp or grommet hole mounting (hardware included).

The TAA compliant ARMDUALPS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Mount dual displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your displays for dual-screen access in a media room
- Spread displays apart or position them back to back for multi-user workstations
- Rotate displays to portrait orientation for web design and coding

### Features

- Create a sleek dual-monitor setup for monitors up to 27"
- Dual articulating monitor arms provide a wide range of motion plus height adjustment
- Easy tool-less assembly with fully assembled desk clamp and pole, plus quick slide-and-click connections
- Adjust your viewing angle with tilt, pan and rotation
- Robust and stable aluminum design supports VESA mount displays (75x75, 100x100) with maximum weight of 22 lb. (10 kg) per display

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	2
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)
<b>Performance</b>	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Display Pan	+180° / -180°
	Display Rotation	360°
	Display Tilt	+90° / -15°
	Maximum Arm Extension	16.5 in [420 mm]
	Maximum Arm Span	37 in [940 mm]
	Maximum Display Size	27in
	Minimum Display Size	13"
<b>Physical Characteristics</b>	Weight Capacity (Per Display)	22.1 lb [10 kg]
	Color	Silver
	Enclosure Type	Aluminum
	Product Height	20.5 in [520 mm]
	Product Length	8.7 in [220 mm]
	Product Width	7.5 in [190 mm]
<b>Packaging Information</b>	Weight of Product	158.2 oz [4482 g]
	Package Height	18.3 in [465 mm]
	Package Length	12.6 in [320 mm]
	Package Width	5.7 in [145 mm]
<b>What's in the Box</b>	Shipping (Package) Weight	194.1 oz [5500 g]
	Included in Package	4 - Swivel Arms 2 - VESA Monitor Mounts 1 - Shoulder

- 1 - Desk Clamp and Pole Assembly
- 2 - M3 Hex Keys
- 1 - EVA Cushion
- 8 - Thumbscrews
- 1 - Cable-Management Clip
- 1 - User Manual

---

Product appearance and specifications are subject to change without notice.