

## Dual-Monitor Stand - Articulating - Steel & Aluminum

Product ID: ARMDUALSS



Customize your workstation, and free up space, with this dual-monitor stand. Mount two monitors on the dual articulating monitor arms, and adjust your displays for optimum viewing with a wide range of motion. The free-standing base gives you flexibility in placing your setup within your workspace.



### Enhance Your Productivity

Work more efficiently with a dual-monitor setup. The horizontal dual-monitor stand lets you mount two VESA mount (75x75, 100x100 mm) monitors, up to 32", with a maximum weight capacity of up to 17.6 lb./8 kg per display.

## Create a More Ergonomic Workspace

Mounting your displays on a dual-monitor stand above the desk surface enables you to adjust your display height, position and viewing angles for an ergonomic workspace. The swiveling arms provide maximum viewing flexibility, letting you work in comfort.

## Height-Adjustable Monitor Mount

It's easy to customize your setup, placing your monitors at the ideal height. Simply adjust the display height along the 16.7" (42.4 cm) pole. You can align your monitors perfectly with the micro-adjustment feature.

## Enjoy Optimum Viewing

Extend the dual articulating arms up to 18.4" (46.8 cm) to position your monitors in the ideal position. Tilt your monitors +90/-40 degrees and swivel +90/-90 degrees for ideal viewing. Rotate your displays for portrait or landscape viewing.

## Keep Cables Out of View

Neatly route your cables, keeping them organized and out of view, with the cable-management channels.

ARMDUALSS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Rotate displays to portrait orientation for web design and coding
- Position displays apart or back to back for multi-user workstations
- Ideal for health care centers, commercial and other busy environments

### Features

- Save space by mounting two monitors up to 32" (up to 17.6 lb./8 kg per display) on a single base
- Dual articulating arms provide a wide range of motion
- Freestanding monitor stand with adjustable height along the 16.7" (42.4 cm) pole
- Landscape to portrait screen rotation, plus +90/-40 degree tilt and +90/-90 degree swivel
- Maximum arm extension of 16.6" (42.2 cm)

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	2
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Desktop Stand
	Orientation	Horizontal
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
<b>Performance</b>	Display Pan	+/- 90°
	Display Rotation	+180° / -180°
	Display Tilt	+90° / -40°
	Height Adjustment	Yes
	Maximum Arm Extension	16.6 in [422 mm]
	Maximum Display Size	32in
	Weight Capacity (Per Display)	17.7 lb [8 kg]
<b>Physical Characteristics</b>	Color	Black & Silver
	Enclosure Type	Aluminum, Steel and Plastic
	Product Height	23.2 in [590 mm]
	Product Length	33.9 in [860 mm]
	Product Width	11.4 in [290 mm]
	Weight of Product	146.5 oz [4150 g]
<b>Packaging Information</b>	Package Height	3.9 in [10 cm]
	Package Length	21.7 in [550 mm]
	Package Width	12.3 in [312 mm]
	Shipping (Package) Weight	183.7 oz [5205 g]
<b>What's in the Box</b>	Included in Package	2 - Swivel Arms 1 - Pole 1 - Base 1 - Shoulder 1 - Cable-Management Clip

- 2 - VESA Mounts
- 8 - M4 x 12 mm Screws
- 8 - M4 x 16 mm Screws
- 8 - M5 x 12 mm Screws
- 8 - M5 x 16 mm Screws
- 8 - M4 x 20 mm Screws
- 8 - M5 x 20 mm Screws
- 8 - Washers
- 16 - Spacers
- 1 - 3 mm Hex Key
- 1 - 4 mm Hex Key
- 1 - 6 mm Hex Key
- 1 - User Manual

---

Product appearance and specifications are subject to change without notice.