

Dual Monitor Desk Mount - Vertical

Product ID: ARMDUALV



This sturdy and sleek dual-monitor mount raises two displays off the surface of your desk or table, to save space while increasing your productivity. With its steel construction, the dual-monitor mount attaches easily to your desk or table to securely hold two monitors, each up to 27", stacked vertically.



Configure your displays to enhance productivity

The dual-monitor mount holds two displays, one above the other, in a vertical configuration. The height of the monitors can be adjusted, as required, along the 27.5" (700 mm) pole.

With the dual-monitor mount, you can work more comfortably, reducing neck and eye strain without having to look side to side when comparing files or reviewing reference material on your screens. It's ideal for numerous applications including web design, coding, creating and reviewing files, and many others. The monitor mount saves valuable desk space and lets you work clutter-free, which is a welcome addition in numerous office environments including business, healthcare, and financial settings.

Adjust your screens to the ideal position

The monitor mount enables smooth, effortless +45°/-45° tilt and +45°/-45° swivel, making it easy to reduce glare and find the perfect viewing angle. It can also rotate a full 360° giving you flexible viewing options.

Rugged steel design

The heavy-duty steel monitor mount holds your two monitors securely in place to protect your investment, and provide long-lasting performance. The dual-monitor mount supports two displays 13" to 27" (330 to 686 mm) in size and 22.1 lb. (10 kg) in weight per monitor. The surface finish features a powder coating to help resist scratches.

Easy installation

The dual-monitor mount makes it easy to mount your VESA mount compatible displays above your desk, table or other surfaces, using the included C-clamp or grommet mount. For easier mounting, the VESA mount features notches that let you pre-set the mounting screw, then slide the monitor into place and tighten the screw. To help keep your work area free of clutter, the monitor mount also features cable clips that keep your cables neatly out of sight.

The ARMDUALV is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Stack your displays one on top of the other, ideal for web design or coding
- Increase your comfort when working on two screens to create files or compare documents
- Enhance your productivity in office settings including business, healthcare, financial and real estate
- Save space in your home office

Features

- Mount two monitors vertically to save space and increase your comfort
- Desktop monitor mount supports two displays up to 27" (686 mm) in size and 22.1 lb. (10 kg) in weight per monitor
- Heavy-duty steel construction
- The height of the monitors can be adjusted along the 27.5" (700 mm) pole
- Adjust your screen angle easily with +45°/-45° tilt and +45°/-45° swivel
- Full 360° rotation
- Simple installation (desk C-clamp or grommet mount) and integrated cable management

Hardware	Warranty	2 Years
	# of Displays Supported	2
	Mounting Options	Desk & Grommet Clamp
	Orientation	Vertical
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Maximum Display Size	27in
	Minimum Display Size	13"
	Mounting Surface Thickness	10 mm to 88 mm
	Swivel / Pivot	+45° / -45°
	Tilt	+ 45° / - 45°
	Weight Capacity (Per Display)	22.1 lb [10 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	35.4 in [900 mm]
	Product Length	4.7 in [120 mm]
	Product Weight	7.5 lb [3.4 kg]
	Product Width	4.6 in [116 mm]
Packaging Information	Shipping (Package) Weight	9.4 lb [4.3 kg]
What's in the Box	Included in Package	1 - lower pole
		1 - upper pole
		1 - desk clamp
		1 - grommet collar
		2 - VESA monitor mounts
		1 - pole connector
		2 - cable-management clips
		1 - cap
5 - rubber pads		

- 1 - grommet plate
- 1 - 3 mm hex key
- 1 - 5 mm hex key
- 1 - 6 mm hex key
- 8 - M4x12 mm screws
- 8 - M5x12 mm screws
- 8 - washers
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.