

Monitor Desk Mount

Product ID: ARMPIVOT



The ARMPIVOT Adjustable Monitor Arm lets you mount a display to your desk or table on a simple yet stylish monitor pole, with tilt, pivot and height adjustments. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The desk-mount monitor arm features an 11.89in (302mm) tall support post, for a much greater height adjustment range than a typical monitor stand can provide. For viewing longer pages or blocks of code without scrolling, the LCD arm also supports landscape to portrait display rotation.

Mounting your displays on a support post above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment, with the added benefit of reclaiming valuable workspace on your desk.



Supporting 12 - 30" displays up to a maximum weight capacity of 30lbs (14kg), the monitor mount holds your display with ease, and integrates a cable management hook to keep things neat. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk, table or mount through a grommet hole.

Backed by a StarTech.com 5-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount a display to the side of your desk or table with tilt, swivel and height adjustment capabilities
- Grommet mount your display through a desk or above a server cabinet and position as needed
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate displays to portrait orientation for web design and coding

Features

- Adjustable monitor arm with several position / viewing angle adjustments
- Supports displays from 12 to 30" (30lbs / 14kg capacity)
- TAA compliant for GSA Schedule purchases
- 360° rotation around the support post
- +90/-15° Tilt
- Landscape to portrait screen rotation
- Includes convertible desk / grommet-mount clamp
- Clamp fits desks up to 4in (101mm) thick
- Integrated cable management

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	No
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Display Size	30in
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Table Hole for Grommet Mount: 0.39 - 2.36 in. (10 - 60 mm)
	Swivel / Pivot	360° around the support post
	Tilt	+90° / -15°
	Weight Capacity (Per Display)	30.9 lb [14 kg]
Physical Characteristics	Color	Silver
	Enclosure Type	Steel and Plastic
	Product Weight	4.4 lb [2 kg]
Packaging Information	Shipping (Package) Weight	5.7 lb [2.6 kg]
What's in the Box	Included in Package	1 - Support Post 1 - Monitor Mount 1 - Large C Clamp 1 - Small C Clamp 1 - Hand Screw 1 - Pressure Plate 4 - Thumb Screws 4 - M6x12mm Phillips Screws 4 - M5x14mm Hex Screws 1 - M4x15mm Phillips Screw

- 1 - Male Round Washer
- 1 - Female Round Washer
- 1 - Cable Clip
- 1 - EVA Cushion
- 1 - M3 (2.5mm) Allen Wrench
- 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.