

Desk-Mount Monitor Arm - Articulating - Heavy Duty Steel

Product ID: ARMPIVOTB



Save valuable desk space and position your monitor in a more comfortable viewing position. This durable desk-mount monitor arm makes it easy to suspend your display above your work area. It features an articulating arm that enables you to tilt, swivel and rotate your screen, to create a more ergonomic workspace and enhance productivity.



Mount your monitor to save valuable space

The single-monitor mount enables you to free up desk space by raising your screen off of your desk. It gives you more room to work by removing the monitor's bulky base from your desk surface. It's a quick and cost-effective way to maximize your available desk space, which makes for a more comfortable workstation and a more productive work environment.



Adjust the position of your monitor with ease

The articulating arm gives you maximum workspace flexibility. You can extend the arm up to 17" (428 mm), along with swivel (180 degrees) and tilt (up to 90 degrees) adjustments that make it easy to find the perfect viewing angle. The arm offers smooth 360-degree screen rotation, so it's easy to switch from landscape to portrait orientation, to best meet your work requirements. You can also adjust the height of your monitor along the pole to your desired viewing position, to a maximum height of 17.7" (450 mm).

Rugged Steel Design

With its heavy-duty solid steel construction, the monitor mount provides long-lasting performance. The monitor arm supports a flat-panel display 13" to 27" (330 to 685.8 mm) in size and up to 17.6 lb. (8 kg) in weight.

Easy installation

The single-monitor arm makes it easy to mount your VESA mount compatible display above your desk, table or other surfaces, using the included C-clamp or grommet mount. For easier mounting, the VESA mount features notches that let you pre-set the mounting screw, then slide the monitor in place and tighten the screw. To help keep your work area free of clutter, the monitor arm also features cable clips that keep your cables neatly out of sight.

The ARMPIVOTB is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a more ergonomic workspace in office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

Features

- Desk-mount monitor arm supports displays up to 27" (685.8 mm) in size and 17.6 lb. (8 kg) in weight
- Articulating arm lets you adjust your viewing angle with 180° swivel and + 45° / - 45° tilt
- Arm extension up to 17" (428 mm)
- Maximum height adjustment of 17.7" (450 mm)
- Heavy-duty steel construction
- Switch easily from landscape to portrait position with full 360° rotation
- Adjustable height
- Simple installation (desk C-clamp or grommet mount) and integrated cable management

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Arm Extension	16.9 in [428 mm]
	Maximum Display Size	27in
	Maximum Height	17.7 in [450 mm]
	Minimum Display Size	13"
	Swivel / Pivot	180°
	Tilt	+ 45° / - 45°
Weight Capacity (Per Display)	17.7 lb [8 kg]	
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	17.6 in [446 mm]
	Product Length	4.3 in [108 mm]
	Product Weight	6.7 lb [3 kg]
	Product Width	18.2 in [462 mm]
Packaging Information	Shipping (Package) Weight	6.8 lb [3.1 kg]
What's in the Box	Included in Package	1 - monitor arm 1 - pole 1 - desk clamp 1 - cable-management clip 1 - grommet baseplate 5 - rubber pads

1 - desk-clamp screw

1 - grommet plate

1 - 5 mm hex key

1 - 6 mm hex key

4 - M4x12 mm screws

4 - M5x12 mm screws

4 - washers

1 - instruction manual

Product appearance and specifications are subject to change without notice.