

Desk Mount Monitor Arm - Articulating - Aluminum - Premium

Product ID: ARMPIVOTB2



Save space with this premium desk-mount monitor arm, by suspending your display above your desk. It supports a monitor up to 30", with an articulating arm that makes it easy to adjust your screen.



Versatile Use

Use the single monitor desk mount to mount your VESA mount monitor (75x75, 100x100) up to 30". You can also mount your Apple Cinema Display, 24-inch iMac or 27-inch iMac, or Thunderbolt Display that came with a removable stand or built-in VESA mount adapter. The attractive silver finish complements Apple displays, making it ideal for customer-facing workstations.

Sleek and Stable Aluminum Design

Made of aluminum, the heavy-duty monitor arm provides stable support for your display, with a weight capacity of up to 30.9 lb. (14 kg).



Enjoy Optimum Viewing

The arm extends 8.3" (210 mm) to allow a wide range of motion. Move the monitor arm effortlessly side to side to adjust your screen position.

With its articulating arm, the monitor mount makes it easy to find the right viewing angle. Pan a full +180/-180 degrees left or right and tilt your display +90/-15 degrees to adjust the angle up or down. For landscape or portrait viewing, rotate your display 360 degrees.

Height Adjustment

Work in comfort. This height adjustable computer monitor arm lets you raise or lower the monitor arm along the pole, with a range of up to 7.87" (200 mm).

Tool-less Assembly

Quick slide-and-click connections ensure easy assembly and save time when setting up multiple units. The computer screen mount gives you the option of desk-clamp or grommet-hole mounting. Hardware is included for all mounting options.

The TAA compliant ARMPIVOTB2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount your VESA mount display iMac, Apple Cinema and Thunderbolt Displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your display to your desk in a cubicle workstation to save space
- Create a more ergonomic workspace in the business office or home office

Features

- Save space by mounting a display up to 30", including VESA mount, iMac, Apple Cinema and Thunderbolt Displays (hardware included)
- Articulating arm for easier monitor adjustment plus height adjustable along the pole
- Easy tool-less assembly with quick slide-and-click connections
- Adjust your viewing angle with tilt, pan and rotation
- Robust and stable aluminum display mount supports maximum weight of 30.9 lb. (14 kg)

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
Performance	Display Pan	+180° / -180°
	Display Rotation	360°
	Display Tilt	+90° / -15°
	Maximum Display Size	30in
	Weight Capacity (Per Display)	30.9 lb [14 kg]
Physical Characteristics	Product Height	18.1 in [460 mm]
	Product Length	8.7 in [220 mm]
	Product Width	5.1 in [130 mm]
	Weight of Product	113 oz [3200 g]
Packaging Information	Package Height	5.7 in [145 mm]
	Package Length	18.5 in [470 mm]
	Package Width	9.1 in [230 mm]
	Shipping (Package) Weight	114.4 oz [3240 g]
What's in the Box	Included in Package	1 - Monitor Mount Assembly 1 - Swivel Arm 1 - Pole-and-Clamp Assembly 4 - Surface Protectors 1 - Flange Mount 1 - Torx Key 1 - 3mm Hex Key 1 - 4mm Hex Key 1 - Access Card 2 - Monitor Mount Screws 4 - VESA Screws

Product appearance and specifications are subject to change without notice.