

Desk-Mount Monitor Arm - Full Motion - Articulating

Product ID: ARMPIVOTE



The ARMPIVOTE Articulating Monitor Arm lets you mount a display to your desk or table, with extension, tilt, pan, swivel, pivot and gas-spring height adjustments.

The desk-mount monitor arm features a gas-spring cylinder to raise or lower your display with minimal effort, plus it offers a wide range of motion on several axes. For viewing longer pages or blocks of code without scrolling, the LCD arm also supports landscape to portrait display rotation.

Mounting your displays on a monitor arm above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment, with the added benefit of reclaiming valuable workspace on your desk.

Supporting 12 - 24" displays up to a maximum weight capacity of 8 lb. (3.6 kg), the monitor mounting arm holds your display with ease, and integrates a cable management channel to keep things neat. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk / table or mount through a grommet hole, for a versatile monitor mounting solution.

Backed by a StarTech.com 2-year warranty and free, lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Mount a display to the side of your desk or table with a wide range of adjustment capability
- Grommet mount your display through a desk or above a server cabinet and position as needed
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate displays to portrait orientation for web design and coding

Features

- Articulating monitor arm with a wide range of motion
- Gas-spring height adjustment cylinder
- Supports displays from 12 to 24" (8 lb. / 3.6 kg weight capacity per display)
- 360° rotation around the support post and at the elbow
- +/-90° Tilt and +/-90° Pan
- Maximum arm extension of 22.05in (560mm)
- Landscape to portrait screen rotation
- Includes convertible desk / grommet-mount clamp
- Clamp fits desks up to 2.95in (75mm) thick
- Integrated cable management

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Arm Extension	22 in [560 mm]
	Maximum Display Size	24in
	Mounting Surface Thickness	0.39 - 2.95in (10 - 75mm)
	Pan	+/- 90°
	Swivel / Pivot	360° around the support post 360° at the elbow
	Tilt	+/- 90°
	Weight Capacity (Per Display)	8 lb [3.6 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Weight	5.1 lb [2.3 kg]
Packaging Information	Shipping (Package) Weight	6 lb [2.7 kg]
What's in the Box	Included in Package	1 - Gas Spring Arm 1 - Extension Arm 1 - Support Pole 1 - Clamp 1 - Cover and Bolt 5 - Cable Covers 4 - Spacers 4 - M4x12mm Screws 4 - M4x25mm Screws 1 - Cable Clip

- 2 - Plastic Gasket Cushions
- 1 - 4mm Allen Wrench
- 1 - 6mm Allen Wrench
- 4 - Thumb screws
- 5 - Cable ties
- 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.