

Desk-Mount Monitor Arm - Full Motion - Articulating

Product ID: ARMPIVOTE



The ARMPIVOTE Articulating Monitor Arm lets you mount a display to your desk or table, with extension, tilt, pan, swivel, pivot and gas-spring height adjustments.

The desk-mount monitor arm features a gas-spring cylinder to raise or lower your display with minimal effort, plus it offers a wide range of motion on several axes. For viewing longer pages or blocks of code without scrolling, the LCD arm also supports landscape to portrait display rotation.

Mounting your displays on a monitor arm above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment, with the added benefit of reclaiming valuable workspace on your desk.

Supporting 12 - 24" displays up to a maximum weight capacity of 8 lb. (3.6 kg), the monitor mounting arm holds your display with ease, and integrates a cable management channel to keep things neat. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk / table or mount through a grommet hole, for a versatile monitor mounting solution.

Backed by a StarTech.com 2-year warranty and free, lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Mount a display to the side of your desk or table with a wide range of adjustment capability
- Grommet mount your display through a desk or above a server cabinet and position as needed
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate displays to portrait orientation for web design and coding

Features

- Articulating monitor arm with a wide range of motion
- Gas-spring height adjustment cylinder
- Supports displays from 12 to 24" (8 lb. / 3.6 kg weight capacity per display)
- 360° rotation around the support post and at the elbow
- +/-90° Tilt and +/-90° Pan
- Maximum arm extension of 22.05in (560mm)
- Landscape to portrait screen rotation
- Includes convertible desk / grommet-mount clamp
- Clamp fits desks up to 2.95in (75mm) thick
- Integrated cable management

| | | |
|---------------------------------|-------------------------------|---|
| Hardware | Warranty | 2 Years |
| | # of Displays Supported | 1 |
| | Articulating | Yes |
| | Mounting Options | Desk & Grommet Clamp |
| | VESA Hole Pattern(s) | 75x75 mm 100x100 mm |
| | Wallmountable | No |
| Performance | Display Rotation | 360° |
| | Height Adjustment | Yes |
| | Maximum Arm Extension | 22 in [560 mm] |
| | Maximum Display Size | 24in |
| | Mounting Surface Thickness | Desk Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Table Hole for Grommet Mount: 1.96 - 2.75 in. (50 - 70 mm) |
| | Pan | +/- 90° |
| | Swivel / Pivot | 360° around the support post 360° at the elbow |
| | Tilt | +/- 90° |
| | Weight Capacity (Per Display) | 8 lb [3.6 kg] |
| Physical Characteristics | Color | Black |
| | Enclosure Type | Steel and Plastic |
| | Product Weight | 4.9 lb [2.2 kg] |
| Packaging Information | Shipping (Package) Weight | 6 lb [2.7 kg] |
| What's in the Box | Included in Package | 1 - Gas Spring Arm 1 - Extension Arm 1 - Support Pole 1 - Clamp 1 - Cover and Bolt 5 - Cable Covers 4 - Spacers 4 - M4x12mm Screws 4 - M4x25mm Screws |

- 1 - Cable Clip
- 2 - Plastic Gasket Cushions
- 1 - 4mm Allen Wrench
- 1 - 6mm Allen Wrench
- 4 - Thumb screws
- 5 - Cable ties
- 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.