

Single Desk-Mount Monitor Arm - Full Motion - Heavy-Duty - Black

Product ID: ARMPIVOTHDB



Free up space while creating an ergonomic work environment. This desk-mount monitor arm makes it easy to securely mount your display above your desk or table and adjust the height with one touch. You can mount a display ranging in size from 13" to 32" (330 mm to 813 mm), and the monitor arm features an attractive black finish that complements your workspace.

Mount Your Monitor to Save Space

This heavy-duty monitor arm saves space on your work surface by elevating your monitor above your desk or table.

One-Touch Height Adjustment

The monitor-mount arm features a gas-spring cylinder that makes it easy to raise or lower your display, with up to 13.1" (335 mm) of height adjustment. Adjust the tension according to the weight of your monitor, to re-position the monitor height effortlessly.

Adjust Your Monitor for Ideal Viewing

The full-motion articulating monitor arm extends up to 23.8" (605 mm) so it's easy to find the right viewing angle. Swivel your monitor 180 degrees to share your display, while collaborating with others. Tilt your screen 90 degrees for comfortable viewing or rotate it 180 degrees for landscape or portrait viewing.

Easy Installation

The VESA monitor mount is easy to install (desk C-clamp or grommet mount) and offers built-in cable management. The detachable VESA panel makes it simple to attach or remove your monitor.

ARMPIVOTHDB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use in workstations with multiple users
- Add comfort to office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

Features

- Single-monitor arm saves space by letting you mount a monitor up to 32" (813 mm) weighing up to 19.8 lb. (9 kg)
- Durable, heavy-duty aluminum construction with attractive black finish
- Easy one-touch height adjustment (up to 13.1" /335 mm) with gas spring arm
- Hassle-free installation with detachable VESA panel and integrated cable management
- Articulating arm rotates and swivels 180°, and provides +90° / -90° tilt

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.34 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	180°
	Display Tilt	+/- 90°
	Maximum Arm Extension	23.8 in [605 mm]
	Maximum Display Size	32in
	Maximum Height	19.9 in [505 mm]
	Minimum Display Size	13"
	Minimum Height	6.7 in [170 mm]
	Swivel / Pivot	180°
Weight Capacity (Per Display)	19.9 lb [9 kg]	
Physical Characteristics	Color	Black
	Product Height	20.8 in [52.9 cm]
	Product Length	3.8 in [96 mm]
	Product Width	11.2 in [28.4 cm]
	Weight of Product	6.8 lb [3.1 kg]
Packaging Information	Package Height	0.5 in [12 mm]
	Package Length	19.1 in [48.5 cm]
	Package Width	12.4 in [31.6 cm]
	Shipping (Package) Weight	9.5 lb [4.3 kg]
What's in the Box	Included in Package	1 - Spring Arm 1 - VESA Monitor Mount

- 1 - Grommet Base Plate
- 1 - Grommet Plate
- 1 - L Bracket
- 1 - Desk Clamp
- 1 - Hex Key Holder
- 5 - Clamp Screws
- 1 - Grommet Knob
- 2 - Rubber Pads
- 1 - 4 mm Hex Key
- 1 - 5 mm Hex Key
- 1 - 6 mm Hex Key
- 4 - M4x12 mm Thumbscrews
- 4 - M5x12 mm Screws
- 4 - Washers
- 4 - Spacers
- 1 - Grommet Screw
- 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.