

## Monitor Desk Mount - Heavy-Duty Steel

Product ID: ARMPIVOTV2



Save valuable desk space and position your monitor in a more comfortable viewing position. Constructed of high-grade steel, this monitor desk mount for up to 32" monitors makes it easy to suspend your display above your desk or other work surface.



## **Work in comfort while saving desk space**

Clear up your desk surface while creating an ergonomic workspace. This simple yet rugged monitor mount supports displays 13" to 32" (330 to 813 mm) in size and 17.6 lb. (8 kg) in weight. Easily rotate, tilt and swivel, to adjust your screen position and find the perfect viewing angle. You can also adjust the height of your monitor along the vertical pole to a maximum height of 17.4" (443 mm) to your desired position, to reduce neck and eye strain.

## **Rugged steel construction**

The heavy-duty steel mount is built for long-lasting performance. The surface finish features a powder coating to help resist scratches.

## **Easy installation**

The monitor desk mount makes it easy to mount a VESA mount compatible display above your desk, table or other surface, using the included C-clamp or grommet mount. A detachable VESA panel enables simple attachment of your monitor, then you just slide your monitor onto the mount. To help keep your work area free of clutter, the monitor mount also features cable clips that keep your cables neatly out of sight.

The ARMPIVOTV2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Create a more ergonomic workspace in office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

### Features

- Monitor desk mount supports displays up to 32" (686 mm) in size and 17.6 lb. (8 kg) in weight
- Detachable VESA mount makes it easy to attach your monitor
- Supports VESA mount compliant monitors: 75x75, 100x100
- Heavy-duty steel construction
- Adjustable height up to 17.3" (440 mm) along the vertical pole
- Simple installation (desk C-clamp or grommet mount)
- Cable management

<b>Hardware</b>	Warranty	2 Years
	# of Displays Supported	1
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
<b>Performance</b>	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Arm Extension	3.5 in [88 mm]
	Maximum Display Size	32in
	Maximum Height	17.4 in [443 mm]
	Minimum Display Size	13"
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Table Hole for Grommet Mount: 0.41 - 1.96 in. (10.5 - 50 mm)
	Swivel / Pivot	180°
	Tilt	+ 45° / - 45°
	Weight Capacity (Per Display)	17.7 lb [8 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	5.8 in [148 mm]
	Product Length	21.6 in [548 mm]
	Product Weight	5.2 lb [2.4 kg]
	Product Width	4.5 in [114 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	6.8 lb [3.1 kg]
<b>What's in the Box</b>	Included in Package	1 - VESA monitor mount 1 - VESA pole clamp 1 - pole 3 - pole screws

- 1 - desk clamp
- 1 - grommet plate
- 1 - grommet collar
- 1 - cable-management clip
- 5 - rubber pads
- 1 - thumbscrew
- 1 - 4 mm hex key
- 1 - 6 mm hex key
- 4 - M4x12 mm screws
- 4 - M4x16 mm screws
- 4 - M5x12 mm screws
- 4 - M5x16 mm screws
- 4 - spacers
- 4 - washers
- 1 - instruction manual

---

Product appearance and specifications are subject to change without notice.