

Desktop Monitor Stand - Silver - Works with iMac, Apple Cinema Display and Thunderbolt Display

Product ID: ARMPIVSTND



The adjustable monitor stand lets you mount a display on your desk, with tilt, pivot and height adjustments for perfect positioning.

The monitor stand holds most common displays with ease, supporting monitors from 12 - 30" up to a maximum weight capacity of 30lbs (14kg).

For added flexibility, you can use the included hardware to mount your Apple Cinema Display, Thunderbolt Display or Apple iMac. The stand works with any Apple Cinema Display or Thunderbolt Display that came with a removable stand or built-in VESA mount adapter. It also works with the 24-inch iMac and 27-inch iMac with a removable stand, or with a built-in VESA mount adapter.

The desktop monitor stand features a 15in (380mm) tall support post, for a much greater range of height adjustments than typical monitor stands can provide. For viewing longer pages or blocks of code without scrolling, the LCD stand also supports landscape to portrait display rotation.

Adjust your display height, position and viewing angles easily to create an ergonomic work environment, with the added benefit of reclaiming valuable workspace on your desk by mounting on a support post above the desk surface.

This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The ARMPIVSTND is backed by a StarTech.com 2-year warranty and free, lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Mount a display on your desk or table with tilt, swivel and height adjustment capabilities
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate your display to portrait orientation for web design and coding

Features

- Adjustable monitor stand with several position / viewing angle adjustments
- Supports displays from 12 to 30" (30lbs / 14kg capacity)
- TAA compliant for GSA Schedule purchases
- Includes hardware for mounting an iMac or Apple Cinema Display
- Mounting bracket pans 60° around the support post
- Landscape-to-portrait screen rotation

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	No
	Mounting Options	Desktop Stand
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	ARMPIVSTND is compatible with	<ul style="list-style-type: none"> • 24-inch LED Cinema Display and 27-inch LED Cinema Display • 27-inch Apple Thunderbolt Display • 24-inch iMac and 27-inch iMac with removable stand or built-in VESA mount adapter
	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Display Size	30in
	Pan	60°
	Tilt	+45° / -15°
	Weight Capacity (Per Display)	30.9 lb [14 kg]
Physical Characteristics	Color	Silver
	Enclosure Type	Steel and Plastic
	Product Weight	5.2 lb [2.4 kg]
Packaging Information	Shipping (Package) Weight	7.3 lb [3.3 kg]
What's in the Box	Included in Package	1 - Aluminum Base
		1 - Support Post
		1 - Monitor Mount
		1 - Cable Clip
		1 - Iron Position Ring
		4 - M5x18mm Hex Screws
		1 - Flange
		4 - Plastic Caps
		1 - Torx Tool

- 1 - 3mm Allen Wrench
- 1 - 4mm Allen Wrench
- 1 - Access Card
- 4 - Thumb Screws
- 2 - M6x16mm Screws
- 4 - Rubber Feet
- 1 - Instruction manual

Product appearance and specifications are subject to change without notice.