

Sit-Stand Dual-Monitor Arm

Product ID: ARMSTSCP2



This sit-stand dual-monitor arm transforms your desk or tabletop into a highly productive, ergonomic workstation. The monitor arm features a keyboard tray and easy height adjustment that lets you alternate between sitting and standing, without interrupting your workflow.

Adjust the height with one smooth motion

Adjust your working position, with one smooth motion. Simply lift the work surface up to 17.7" (450 mm), to elevate both your monitor plus your keyboard and mouse. The monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column. You can also adjust the tension to your own preference for easy height adjustment.

Enhance productivity with two monitors

The versatile monitor arm lets you create a productive dual-monitor workstation, supporting two monitors up to 24" (with weight capacity of 17.6 lb./8 kg). Move the swing arm left or right (from -90° to 90°) and lower or raise the arm (from -30° to 65°) to the ideal position. The VESA mount also rotates up to 360° for portrait or landscape orientation.

Ample working space

The monitor arm features a large keyboard tray (17.68 x 8.15" / 449 x 207 mm) with ample working space. A slide-out tray (8.5 x 8.4" / 217 x 213 mm) holds your mouse, on the left or right. You can tuck the monitor arm away when it's not in use, to free up space. The keyboard tray also folds up to 90°.

Flexible installation

The compact sit-stand monitor arm features a grommet assembly and desk-clamp option, to fit easily into your workspace, including space-limited corners.

The ARMSTSCP2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a sit-stand workstation in healthcare environments, cubicles, or offices with limited space
- Provides a cost-effective solution, with clamp or grommet mounting options for existing desks
- Works well with space-limited corner desks

Features

- Turn your desk into an ergonomic workstation with this sit-stand dual-monitor arm, supporting two monitors up to 24" (with weight capacity of 17.6 lb./8 kg).
- The work surface has a height adjustment of up to 17.7" (450 mm)
- Monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column
- Adjust your monitor for ideal viewing, with -15° to +15° swivel and 0° to +30° tilt
- Move the swing arm left or right (from -90° to 90°) and lower or raise the arm (from -30° to 65°) to the ideal position
- Viewing distance: 16.1" (408.7 mm)
- Rotates 360° for landscape or portrait viewing
- Built-in cable management keeps your workstation well organized
- The arm tucks away and the keyboard tray folds up to 90°, saving space when not in use
- Clamp and grommet base options for flexible installation options, including space-limited areas such as desk corners or rear sides
- 100x100 mm, 75x75 mm VESA mount compatible
- TAA compliant

Hardware	Warranty	2 Years
	# of Displays Supported	2
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	100x100 mm 75x75 mm
Performance	Display Rotation	360°
	Display Tilt	+30° / 0°
	Height Adjustment	Yes
	Maximum Display Size	24in
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Grommet Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Table Hole for Grommet Mount: 0.33 - 2.55 in. (8.5 - 65 mm)
	Swivel / Pivot	+90° / -90°
	Weight capacity of keyboard tray with desk clamp	3.3 lb. (1.5 kg)
	Weight capacity of keyboard tray with grommet mount	5.6 lb. (2.5 kg)
Weight capacity of monitor arm	17.6 lb. (8 kg)	
Physical Characteristics	Color	Black
	Enclosure Type	Steel, Aluminum and Plastic
	Product Height	35 in [89 cm]
	Product Length	37 in [94 cm]
	Product Width	30.4 in [77.3 cm]
	Weight of Product	26.5 lb [12 kg]
Packaging Information	Package Height	8.4 in [21.4 cm]
	Package Length	34.9 in [88.7 cm]
	Package Width	15.8 in [40.2 cm]
	Shipping (Package) Weight	26.5 lb [12 kg]
What's in the Box	Included in Package	1 - monitor arm 1 - column

- 1 - keyboard tray
- 1 - keyboard tray cap
- 1 - base
- 2 - VESA monitor mounts
- 1 - plastic washer
- 1 - metal washer
- 1 - M8x65 mm screw
- 1 - M8x20 mm screw
- 2 - M6x25 mm screws
- 4 - M6x12 mm screws
- 5 - M6x10 mm screws
- 8 - M4x10 mm screws
- 4 - base screws
- 1 - 2.5 mm hex key
- 1 - 5 mm hex key
- 1 - 6 mm hex key
- 1 - adhesive strip
- 1 - socket driver
- 1 - base pad
- 1 - base plate
- 1 - grommet plate
- 4 - clamp screws
- 1 - clamp L bracket
- 1 - clamp screw assembly
- 2 - knobs
- 2 - crossbar washers
- 2 - crossbars
- 1 - crossbar mount
- 1 - wrench
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.