

Wall-Mount Monitor Arm - 10.2" (26 cm) Swivel Arm - Premium

Product ID: ARMWALLDS2



Free up space with this wall-mount monitor arm and enjoy optimum viewing with the swiveling extension arm. The premium design ensures smooth, effortless motion and makes it easy to reposition your display, to work in comfort or collaborate with others. The attractive silver finish complements your decor.

The wall-mount system is ideal for business, healthcare, financial or other settings, where you may want to share your screen, or for customer-facing interactive displays.



Adjust the Swivel Arm with Ease

The wall-mount monitor arm extends 10.2" (26 cm), making it easy to change your screen position. Move the swivel wall-mount freely, to the left or right. You can also adjust the swivel tension.

Durable and Stable Construction

The robust aluminum design provides a stable wall-mount for your computer monitor or flat-screen TV up to 30". It's ideal for touch-screen stability. The universal display wall mount supports VESA mount monitors (75x75, 100x100) up to 30.9 lb. (14 kg) in weight.

Adjust your Viewing Angle

Share your screen with ease. The display wall mount offers a full +180-degree/-180-degree pan, to move your screen left or right. It tilts freely +90/-15-degrees, to adjust the angle up or down. Rotate your screen for landscape or portrait viewing.



Low-Profile Design

Push the swivel arm back to the wall, so your monitor sits just 5" (129 mm) from the wall when not in use.

Tool-less Assembly

The quick slide-and-click connections make the monitor wall mount easy to assemble and saves time when setting up multiple units.

The TAA compliant ARMWALLDS2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up space in business, commercial, industrial or office settings
- Share your screen with clients or visitors in office settings such as healthcare or financial
- Works well in non-desk environments as well as public places

Features

- Wall-mount a single display up to 30" to save space and easily share your screen
- Swivel arm extends 10.2" (26 cm) and features two swivel points for flexible viewing
- Easy tool-less assembly with quick slide-and-click connections
- Adjust your viewing angle with +180°/-180° pan, +90°/-15°tilt, and rotation
- Robust and stable aluminum design supports VESA mount displays (75x75, 100x100) with maximum weight of 30.9 lb. (14 kg)

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Articulating	No
	Cable Management	Yes
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
Performance	Display Pan	+180° / -180°
	Display Rotation	360°
	Display Tilt	+90° / -15°
	Height Adjustment	No
	Maximum Arm Extension	10.2 in [260 mm]
	Maximum Display Size	30in
	Minimum Display Size	13"
	Swivel / Pivot	+180°/-180° at the wall 360° at the elbow
Physical Characteristics	Weight Capacity (Per Display)	30.9 lb [14 kg]
	Color	Silver
	Enclosure Type	Aluminum
	Product Height	13 in [330 mm]
	Product Length	6.9 in [176 mm]
	Product Width	5.4 in [136 mm]
Packaging Information	Weight of Product	42.4 oz [1200 g]
	Package Height	3.9 in [100 mm]
	Package Length	13.4 in [340 mm]
	Package Width	7.4 in [188 mm]
What's in the Box	Shipping (Package) Weight	53.7 oz [1520 g]
	Included in Package	1 - Wall Mount
		1 - Swivel Arm
		1 - Monitor Mount
		1 - M3 Hex Key

- 4 - Thumb Screws
- 2 - Wall Plugs
- 2 - Mounting Screws
- 1 - User Manual

Product appearance and specifications are subject to change without notice.